

SMP Female Non-Magnetic Connector Solder Attachment for PE-SR047-NM



PE517813

Configuration

- SMP Female Connector
- 50 Ohms
- Straight Body Geometry
- Connector Interface Types: PE-SR047-NM
- Non-Magnetic Design

Features

- Max. Operating Frequency 40 GHz
- Excellent VSWR of 1.2:1
- Gold Plated Beryllium Copper Contact
- Blind Mate Connector

Applications

- General Purpose Test
- Custom Cable Assemblies

Description

Pasternack's PE517813 SMP Female Connector Solder Attachment for PE-SR047-NM Cable, is part of our full line of RF components available for same-day shipping. Our SMP female connector operates up to a maximum frequency of 40 GHz and offers excellent VSWR of 1.2:1. The Pasternack blind mate connector is ideal for applications where direct visual or tactile access to the connection point is not possible, for example, when two circuit boards need to be mated.

Our SMP female connector PE517813 datasheet specifications and drawing with dimensions are shown below in this PDF. Pasternack's broad catalog of RF, microwave and millimeter wave connectors allows designers to configure and customize their signal connections however they like. Whether the need is to provide an I/O for a board design, or simply create a custom cable assembly configuration, Pasternack has the right connector for the job. Pasternack can also expertly build your custom cable assemblies for you and ship same-day.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		40	GHz
VSWR			1.2:1	
Insertion Loss			0.18	dB
Impedance		50		Ohms

Electrical Specification Notes:

Insertion Loss is equal to $0.03 \times \sqrt{\text{FGHz}}$

Mechanical Specifications

Size

Length	0.135 in [3.43 mm]
Width	0.135 in [3.43 mm]
Height	0.28 in [7.11 mm]
Weight	0.005 lbs [2.27 g]

SMP Female Non-Magnetic Connector
Solder Attachment for PE-SR047-NM



PE517813

Material Specifications

Description	Material	Plating
Contact	Beryllium Copper	Gold
Outer Conductor	Beryllium Copper	Gold
Body	Beryllium Copper	Gold

Environmental Specifications

Temperature

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

SMP Female Non-Magnetic Connector Solder Attachment for PE-SR047-NM from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SMP Female Non-Magnetic Connector Solder Attachment for PE-SR047-NM PE517813](#)

URL: <https://www.pasternack.com/smp-female-pe-sr047-nm-connector-pe517813.html>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

PE517813 CAD Drawing

SMP Female Non-Magnetic Connector Solder Attachment for PE-SR047-NM

