

Commercial Grade Bulkhead Mount Insulated Ground TNC Female to TNC Female Adapter

PE910072



Configuration

- TNC Female Connector 1
- TNC Female Connector 2
- 50 Ohms Impedance
- Commercial Grade Design
- Straight Body Geometry
- Bulkhead Mount Method

Features

- Insulated Ground
- Gold Plated Phosphor Bronze Contact

Applications

- General Purpose Test
- Rack Mounted Equipment

Description

Pasternack's PE910072 bulkhead insulated ground TNC female to TNC female adapter is part of our full line of RF components available for same-day shipping. Our TNC to TNC adapter has a female to female gender configuration in a commercial grade design. This RF TNC bulkhead to TNC adapter allows designers to create external connections on their product enclosures, and can be used in a variety of other rack mount and panel mount applications.

RF adapters are often used to enable connections between two connector types that would otherwise not mate. Certain adapter configurations can also be used to protect connectors on expensive equipment where the number of connect/disconnect cycles is high. An RF, microwave or millimeter wave adapter is connected to the equipment, and the commonly changed connection is made with the adapter which can be easily replaced when it wears out after high usage; such adapters are referred to as connector savers. Pasternack also offers bulkhead, panel mount, hermetically sealed, reverse polarity, and isolated ground adapter varieties to serve all of your RF, microwave and millimeter wave needs.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Impedance		50		Ohms

Mechanical Specifications

Size	
Length	1.28 in [32.51 mm]
Width	0.61 in [15.49 mm]
Height	0.61 in [15.49 mm]
Weight	0.02 lbs [9.07 g]

Description	Connector 1	Connector 2
Polarity	Standard	Standard
Connector Option	Insulated Ground	Isolated Ground

Material Specifications

Description	Connector 1		Connector 2	
	Material	Plating	Material	Plating
Type	TNC Female		TNC Female	

Commercial Grade Bulkhead Mount Insulated Ground TNC Female to TNC Female Adapter



PE910072

Material Specifications

Description	Connector 1		Connector 2	
	Material	Plating	Material	Plating
Contact	Phosphor Bronze	Gold	Phosphor Bronze	Gold
Insulation	ABS		ABS	
Outer Conductor	Brass	Nickel	Brass	Nickel
Body	Brass	Nickel	Brass	Nickel
Gasket	Rubber			
Washer	Steel	Nickel		
Coupling Nut	Brass	Nickel		

Compliance Certifications (see product page for current document)

Commercial Grade Bulkhead Mount Insulated Ground TNC Female to TNC Female Adapter from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Commercial Grade Bulkhead Mount Insulated Ground TNC Female to TNC Female Adapter PE910072](#)

URL: <https://www.pasternack.com/commercial-grade-bulkhead-mount-insulated-ground-tnc-female-to-tnc-female-adapter-pe910072.html>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

PE910072 CAD Drawing

Commercial Grade Bulkhead Mount Insulated Ground TNC Female to TNC Female Adapter

