



### 2.92mm Female to 2.4mm Male Adapter

#### **TECHNICAL DATA SHEET**

PE91296

Configuration

Connector 1
Impedance 1
Connector 2
Impedance 2
Adapter Design
Body Style

2.92mm Female
50 Ohms
2.4mm Male
50 Ohms
Standard
Standard
Straight

**Electrical Specifications** 

Frequency Range DC to 40 GHz
Maximum VSWR 1.15:1

**Mechanical Specifications** 

Size

Length, in [mm] 0.752 [19.1]

**Connector 1** 

Type 2.92mm Female
Mating Cycles 500
Inner Conductor Material and Plating Beryllium Copper, Gold
Inner Conductor Plating Specification MIL-G-45204
Torque, in-lbs [Nm] 8 [0.9]

Body Material and Plating Passivated Stainless Steel

Dielectric Type Ultem 1000

**Connector 2** 

Type 2.4mm Male Mating Cycles 500

Inner Conductor Material and Plating

Inner Conductor Plating Specification

Beryllium Copper, Gold

MIL-G-45204

Inner Conductor Plating Specification MIL-G-4520
Torque, in-lbs [Nm] 8 [0.9]

Body Material and Plating Passivated Stainless Steel

Dielectric Type Ultem 1000

**Environmental Specifications** 

Temperature

Operating Range -55 to +150 deg C

Compliance Certifications (visit www.Pasternack.com for current document)

Not RoHS Compliant

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: 2.92mm Female to 2.4mm Male Adapter PE91296

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com





## 2.92mm Female to 2.4mm Male Adapter

### **TECHNICAL DATA SHEET**

PE91296

#### **Plotted and Other Data**

Notes:

• Values at +25 °C, sea level

2.92mm Female to 2.4mm Male Adapter from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: 2.92mm Female to 2.4mm Male Adapter PE91296

URL: http://www.pasternack.com/2.92mm-female-2.4mm-male-straight-adapter-pe91296-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

# **PE91296 CAD Drawing** 2.92mm Female to 2.4mm Male Adapter

