

## SC Female to SC Female Adapter



# RF Adapters Technical Data Sheet

PE9404

#### Configuration

- SC Female Connector 1
- SC Female Connector 2

#### **Features**

- Max VSWR of 1.25:1 up to 11 GHz
- SC interface compliant with MIL-STD-348
- Contact plating according to QQ-S-365
- Silver Plated Beryllium Copper Contact

- 50 Ohm
- Straight Body Geometry
- SC Interface compliant with MIL-STD-348
- Silver Plated Beryllium Copper Contact
- Contact Plating per QQ-S-365

### **Applications**

- General Purpose Test
- General Purpose Test

#### Description

Pasternack's PE9404 SC female to SC female adapter is part of our full line of RF components available for same-day shipping. Our SC to SC adapter has a female to female gender configuration. PE9404 SC female to SC female adapter operates to 11 GHz. The Pasternack RF adapter provides excellent VSWR of 1.25:1 maximum.

RF adapters are often used to enable connections between two connector types that would otherwise not mate. Certain adapter configurations can also be used to protect connectors on expensive equipment where the number of connect/disconnect cycles is high. An RF, microwave or millimeter wave adapter is connected to the equipment, and the commonly changed connection is made with the adapter which can be easily replaced when it wears out after high usage; such adapters are referred to as connector savers. Pasternack also offers bulkhead, panel mount, hermetically sealed, reverse polarity, and isolated ground adapter varieties to serve all of your RF, microwave and millimeter wave needs.

#### **Electrical Specifications**

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		11	GHz
VSWR			1.25:1	
Operating Voltage (AC)			1,000	Vrms
Dielectric Withstanding Voltage (AC)			3,000	Vrms
Insulation Resistance	5,000			MOhms

Electrical Specification Notes: Values at 25°C, sea level

### **Mechanical Specifications**

Size

 Length
 1.608 in [40.84 mm]

 Width
 0.75 in [19.05 mm]

 Weight
 0.105 lbs [47.63 g]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: SC Female to SC Female Adapter PE9404

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com



## SC Female to SC Female Adapter



# RF Adapters Technical Data Sheet

PE9404

Description	Connector 1	Connector 2	
Туре	SC Female	SC Female	
Polarity	Standard	Standard	
Interface Specification	MIL-STD-348	MIL-STD-348	

#### **Material Specifications**

	Connector 1		Connector 2	
Description	Material	Plating	Material	Plating
Туре	SC Female		SC Female	
Contact	Beryllium Copper	Silver	Beryllium Copper	Silver
		QQ-S-365		QQ-S-365
Insulation	PTFE		PTFE	
Outer Conductor	Brass	Nickel	Brass	Nickel
		QQ-N-290		QQ-N-290
Body	Brass	Nickel	Brass	Nickel

# **Environmental Specifications Temperature**

Operating Range

-65 to +165 °C

Compliance Certifications (see product page for current document)

#### **Plotted and Other Data**

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: SC Female to SC Female Adapter PE9404

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451



## SC Female to SC Female Adapter



## RF Adapters Technical Data Sheet

PE9404

SC Female to SC Female Adapter from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: SC Female to SC Female Adapter PE9404

URL: https://www.pasternack.com/sc-female-sc-female-straight-adapter-pe9404-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451

# PE9404 CAD Drawing

SC Female to SC Female Adapter

