

TRB 3-Slot Plug Non-shorting Dust Cap with 3 Inch Chain



PE610-06304

Features

- Protects against dust and contaminants
- Protects against physical damage
- Nickel Plated Body
- Chain Included

Applications

- General Purpose Laboratory Use
- Test and Measurement

Description

The Pasternack PE610-06304 is a TRB jack RFI cap with a 3-lug bayonet coupling design and a 3-inch stainless steel lanyard. The TRB jack RFI cap has a robust design and is easy to use.

The PE610-06304 RFI cap will keep your sensitive electronics protected from dust and other FOD. This TRB jack RFI cap is included .439-.443-inch d-ring to secure the cap in your assembly. The TRB jack RFI cap is suitable for applications such as aircraft avionics, test labs, the military/aero avionics market, and the avionics test market.

Pasternack has one of the largest in-stock selections of TRB jack RFI caps with same-day shipment. Make your online purchase right now to take advantage of our same-day shipping. For further information on similar products, our expert technical support and knowledgeable sales team can help you get the perfect TRB jack RFI cap for your requirements.

Mechanical Specifications

Configuration

Connector	TRB 3-Slot Plug Non-shorting
Chain Option	3 in Chain
Mating Cycles	500 Cycles

Description	Material	Plating
Body	Brass	Nickel
Coupling Nut	Brass	Nickel
Gasket	Silicone	
Chain	Stainless Steel	Nylon Jacket
Rivet	Brass	Nickel

Size

Length	0.799213 in [20.3 mm]
Width	0.559843 in [14.22 mm]
Height	0.559843 in [14.22 mm]
Weight	0.01 lbs [4.54 g]

Environmental Specifications

Temperature

Operating Range	-65 to 165 deg C
-----------------	------------------

TRB 3-Slot Plug Non-shorting Dust Cap with 3 Inch Chain

**PE610-06304****Compliance Certifications** (see product page for current document)

TRB 3-Slot Plug Non-shorting Dust Cap with 3 Inch Chain from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [TRB 3-Slot Plug Non-shorting Dust Cap with 3 Inch Chain PE610-06304](#)

URL: <https://www.pasternack.com/with-3-inch-chain-dust-cap-pe610-06304-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

PE610-06304 CAD Drawing

TRB 3-Slot Plug Non-shorting Dust Cap with 3 Inch Chain

