



WR-12 Waveguide Magic Tee, UG-387/U Round Cover Flange Operating from 60 GHz to 90 GHz

Waveguide Magic Tees Technical Data Sheet

PEWMT1001

Features

- 60 to 90 GHz Frequency Range
- E to H Port Isolation 25 dB Min
- Collinear Port Isolation 15 dB Min
- 1 dB Insertion loss
- E Band

Applications

- Test and Measurement
- Military Communications
- Commercial Communications
- Wireless Communications
- SATCOM

Description

Pasternack's PEWMT1001 is a magic, or hybrid tee that operates from 60 GHz to 90 GHz, E band. It is a 4 port device that is internally tuned to optimize matching, balance, and isolation. Magic tees have an H-plane (sum) port, an E-plane (difference) port, and two collinear ports. A signal applied to the H port will be equally divided between the two collinear ports. A signal applied to the E port will be divided between the two collinear ports but with a 180 degree phase difference. Similarly, when two in-phase signals of equal amplitude are applied to the collinear ports, these will be added together at the H-plane (sum) port and subtracted from one another at the E-plane (difference) port.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	60		90	GHz
Insertion Loss			1	dB
Isolation, E-H (Difference-Sum) Ports	25			dB
Isolation, Collinear Ports	15			dB

Mechanical Specifications

Size

Weight	0.124 lbs [56.25 g]
Waveguide Size	WR-12
Flange Type	Round Cover
Flange Designation	UG-387/U
Body Material and Plating	Aluminum, Gold
Body Plating Specification	ASTMB488

Environmental Specifications

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:


Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [WR-12 Waveguide Magic Tee, UG-387/U Round Cover Flange Operating from 60 GHz to 90 GHz PEWMT1001](#)



WR-12 Waveguide Magic Tee, UG-387/U Round Cover Flange Operating from 60 GHz to 90 GHz

Waveguide Magic Tees Technical Data Sheet

PEWMT1001



WR-12 Waveguide Magic Tee, UG-387/U Round Cover Flange Operating from 60 GHz to 90 GHz from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [WR-12 Waveguide Magic Tee, UG-387/U Round Cover Flange Operating from 60 GHz to 90 GHz PEWMT1001](https://www.pasternack.com/wr-12-waveguide-magic-tee-ug387-round-90-ghz-pewmt1001-p.asp)


URL: <https://www.pasternack.com/wr-12-waveguide-magic-tee-ug387-round-90-ghz-pewmt1001-p.asp>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PEWMT1001 CAD Drawing

WR-12 Waveguide Magic Tee, UG-387/U Round Cover

Flange Operating from 60 GHz to 90 GHz



LABEL:

P4
PASTERNAK
PEWMT1001
V001186MMDDYYYY
www.PASTERNAK.com
P1 (B. SIDE)
P2
P3

STANDARD TOLERANCES	
.X	±0.2
.XX	±0.01
.XXX	±0.005

*STANDARD TOLERANCES APPLY ONLY TO DIMENSIONS IN INCHES

NOTES:
1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.
2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME
3. DIMENSIONS ARE IN INCHES [mm].

DWG TITLE	PEWMT1001
CAGE CODE	53919
CAD FILE	111417
SCALE	N/A
SIZE	A
	7361

PASTERNAK®
THE ENGINEER'S RF SOURCE
Pasternack Enterprises, Inc.
P.O. Box 16759 | Irvine | CA | 92623
Phone: (949) 261-1920 | Fax: (949) 261-7451
Website: www.pasternack.com | E-Mail: sales@pasternack.com