

8 inch Edge Length, Trihedral Corner Reflector, 1/4-20 Threaded Hole Mount, Aluminum Body



PEWRL0006

Features

- 8" Edge Length
- Compact Size
- High RCS
- Rugged Configuration

Applications

- Radar System Calibration
- Radar System Evaluation
- Radar Target Simulator

Description

Pasternack's PEWRL0006 is an 8" Edge Length Trihedral Corner Reflector with an aluminum construction. PEWRL0006 can be used for Radar systems calibrations and can simulate radar target precisely. The trihedral reflector has a 1/4-20 threaded hole for a built in mounting bracket and can be mounted onto a tripod for rapid system setups.

Product Configuration

Design	Trihedral Corner Reflector
Body Material	Aluminum
Body Plating	Chem Film

Mechanical Specifications

Size


Edge Length	8 in [203.2 mm]
Length	3.84 in [97.54 mm]
Width	8 in [203.2 mm]
Height	6.88 in [174.75 mm]
Weight	0.625 lbs [283.5 g]

8 inch Edge Length, Trihedral Corner Reflector,
1/4-20 Threaded Hole Mount, Aluminum Body



PEWRL0006


Plotted and Other Data



8 inch Edge Length, Trihedral Corner Reflector,
1/4-20 Threaded Hole Mount, Aluminum Body



PEWRL0006



8 inch Edge Length, Trihedral Corner Reflector, 1/4-20 Threaded Hole Mount, Aluminum Body from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [8 inch Edge Length, Trihedral Corner Reflector, 1/4-20 Threaded Hole Mount, Aluminum Body PEWRL0006](https://www.pasternack.com/8-inch-edge-length-trihedral-corner-reflector-aluminum-body-chem-film-finish-pewrl0006-p.aspx)

URL: <https://www.pasternack.com/8-inch-edge-length-trihedral-corner-reflector-aluminum-body-chem-film-finish-pewrl0006-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

8 inch Edge Length, Trihedral Corner Reflector, 1/4-20 Threaded Hole Mount, Aluminum Body

REVISIONS

REV.	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	09/09/19	M.MILLER

UNLESS OTHERWISE SPECIFIED
LEADING DIMENSIONS ARE INCHES
DIMENSIONS IN [] ARE MILLIMETERS

TOLERANCES:

X"±	.2	[5.08]	FRACTIONS	.XX±	.01	[.25]	ANGLES	± 1/32
XXX±	.005	[.13]						

ALL DIMENSIONS SHOWN
ARE FOR REFERENCE ONLY.

THIRD-ANGLE PROJECTION

PASTERNACK
PEWRL0006
D/C: YYWW

THE INFORMATION AND
DESIGN IN THIS DOCUMENT
IS THE PROPERTY OF
PASTERNACK CORPORATION.
ALL RIGHTS RESERVED.

SHEET 1 OF 1

SCALE N/A

THE INFORMATION AND
DESIGN IN THIS DOCUMENT
IS THE PROPERTY OF
PASTERNACK CORPORATION.
ALL RIGHTS RESERVED.

PASTERNACK
an INFINITI brand

Pasternack Enterprises, Inc.
P.O. Box 16759, Irvine, CA 92623
Phone: 1 949 261 1920 | 1 866 727 8376
Fax: 1 949 261 7451
www.pasternack.com | e-mail: sales@pasternack.com

SIZE CAGE PART NUMBER
A 53919 K DANG PEWRL0006

REV A

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT
ADMINISTRATION REGULATIONS, DIVERSION CONTRARY TO U.S. LAW PROHIBITED.