



Tool Kit, Install Tool Kit for LMR-400/600 Connectors (CST-400,CST-600, CT-U, Y1719, Y1720, CCT-02, FKP-01)

Crimp Tools Technical Data Sheet

Features

Configuration

Tool Type	LMR Cable Tool Kit
Hex Size, in	0.429, 0.610
Kit Contents	CST-400,CST-600, CT-U, Y1719, Y1720, CCT-02, FKP-01

Mechanical Specifications

Size	
Length	12 in [304.8 mm]
Width	7.5 in [191 mm]
Height	2 in [50.8 mm]
Weight	0.885 lbs [401.43 g]

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

- Notes:
- Values at +25 °C, sea level

Tool Kit, Install Tool Kit for LMR-400/600 Connectors (CST-400,CST-600, CT-U, Y1719, Y1720, CCT-02, FKP-01) from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Tool Kit, Install Tool Kit for LMR-400/600 Connectors \(CST-400,CST-600, CT-U, Y1719, Y1720, CCT-02, FKP-01\) TK-01](#)

URL: <https://www.pasternack.com/tool-kit-install-tool-kit-for-lmr-400-600-conn-cst-400-cst-600-ct-u-y1719-y1720-cct-02-fkp-01-tk-01-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

1 2 3 4 5 6

REVISION

ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	A	INITIAL RELEASE	03/21/2023	HBAKKE	AGANWANI

TOOL KIT CONTENTS:


PART NUMBER	QUANTITY	DESCRIPTION
CST-400	1	PREP TOOL FOR LMR-400
CST-600	1	PREP TOOL FOR LMR-600
CT-U	1	CRIMP TOOL FOR Y SERIES DIES
Y1719	1	.429" HEX DIES FOR TC/EZ400 CRIMP CONNECTORS
Y1720	1	.610" HEX DIES FOR TC/EZ600 CRIMP CONNECTORS
CCT-02	1	CABLE CUTTING TOOL
FKP-01	1	FIELD KIT TOOL POUCH

UNLESS OTHERWISE SPECIFIED
LEADING DIMENSIONS ARE INCHES
DIMENSIONS IN [] ARE MILLIMETERS

TOLERANCES:
X = ±.2 [.5] FRACTIONS
.XX = ±.02 [.5] ±.132
.XXX = ±.005 [.13] ANGLES ± 1°
CABLE LENGTH TOLERANCES:
≤12 [305] = ±1 [25] / -0
>12 [305] ≤ 60 [1524] = +2 [51] / -0
>60 [1524] ≤ 120 [3048] = +4 [102] / -0
>120 [3048] ≤ 300 [7620] = +6 [152] / -0
>300 [7620] = +5% / -0



Website: www.Pasternack.com
Phone: 1.866.727.8376 | 1.949.261.1920



INTERPRET ALL DIMENSIONS AND
TOLERANCES PER ASME Y14.5

SCALE NONE
SHEET 1 OF 1

DESCRIPTION

Tool, Install tool kit for LMR-400/600 Conn (CST-400, CST-600, CT-U, Y1719, Y1720, CCT-02, FKP-01)

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED.
THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

SIZE A CAGE CODE 53919 DRAWN BY HBAKKE ITEM NO.

TK-01

REV A