


2.92mm Female Bulkhead to 2.92mm Female Bulkhead Cable Using PE-SR405AL Coax



PE3W02444

Configuration

- Connector 1: 2.92mm Female Bulkhead
- Connector 2: 2.92mm Female Bulkhead
- Cable Type: PE-SR405AL
- Coax Flex Type: Semi-Rigid



Applications

- General Purpose
- Laboratory Use

Description

Pasternack's PE3W02444 2.92mm female bulkhead to 2.92mm female bulkhead cable using PE-SR405AL coax is part of our full line of RF components available for same-day shipping. Pasternack's semi-rigid RF cable assemblies are ideal for high performance applications and can be formed, using proper tooling, to the routing pattern required. This Pasternack 2.92mm to 2.92mm cable assembly has a female to female gender configuration with 50 ohm semi-rigid PE-SR405AL coax. Our RF cable assembly with 2.92mm bulkhead interface allows designers to create external connections on their product enclosures, and can be used in a variety of other rack mount and panel mount applications.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Mechanical Specifications

Cable Assembly

| | |
|--------|---------------------|
| Weight | 0.042 lbs [19.05 g] |
|--------|---------------------|

Cable

| | |
|--------------------------------------|---------------------------|
| Cable Type | PE-SR405AL |
| Impedance | 50 Ohms |
| Inner Conductor Type | Solid |
| Inner Conductor Material and Plating | Copper Clad Steel, Silver |
| Dielectric Type | PTFE |
| Number of Shields | 1 |
| Shield Layer 1 | Tinned Aluminum |

2.92mm Female Bulkhead to 2.92mm Female Bulkhead Cable Using PE-SR405AL Coax



PE3W02444

Connectors

| Description | Connector 1 | Connector 2 |
|-------------------------------|------------------------------------|------------------------------------|
| Type | 2.92mm Female Bulkhead | 2.92mm Female Bulkhead |
| Impedance | 50 Ohms | 50 Ohms |
| Configuration | Straight | Straight |
| Contact Material and Plating | Beryllium Copper, Gold over Nickel | Beryllium Copper, Gold over Nickel |
| Contact Plating Specification | 50 μ in minimum | 50 μ in minimum |
| Body Material and Plating | Passivated Stainless Steel | Passivated Stainless Steel |
| Body Plating Specification | SAE-AMS-2700 | SAE-AMS-2700 |

Environmental Specifications

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

2.92mm Female Bulkhead to 2.92mm Female Bulkhead Cable Using PE-SR405AL Coax




PE3W02444

Typical Performance Data

How to Order

Part Number Configuration:



Example: PE3W02444-12 = 12 inches long cable
PE3W02444-100cm = 100 cm long cable

2.92mm Female Bulkhead to 2.92mm Female Bulkhead Cable Using PE-SR405AL Coax from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [2.92mm Female Bulkhead to 2.92mm Female Bulkhead Cable Using PE-SR405AL Coax PE3W02444](#)

URL: <https://www.pasternack.com/2.92mm-female-bulkhead-to-2.92mm-female-bulkhead-cable-using-pe-sr405al-pe3w02444-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

PE3W02444 CAD Drawing

2.92mm Female Bulkhead to 2.92mm Female Bulkhead Cable Using PE-SR405AL Coax

