


COMPONENTS	IMPEDANCE
NMO MOUNT	50 OHM
SMA MALE	50 OHM
RG58	50 OHM



SPECIFICATIONS

FREQUENCY RANGE: DC TO 2.4 GHz



PASTERNACK ENTERPRISES, INC.

P.O BOX 16759, IRVINE, CA 92623
PHONE (949) 261-1920 FAX (949) 261-7451

WEB ADDRESS: www.pasternack.com
E-MAIL ADDRESS: sales@pasternack.com

COAXIAL & FIBER OPTICS

DWG TITLE

PE51022-1

DES. ANTENNA MOUNT (NMO) CABLE ASSEMBLY,
NMO MAGNETIC MOUNT TO SMA MALE, RG58

REV. A **FSCM NO. 53919**

CAD FILE 021508

SCALE N/A

SIZE A 147

NOTES:

1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.
2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.
3. DIMENSIONS ARE IN INCHES.
4. LENGTH TOLERANCE IS $\pm 1.5\%$ OR $3/8"$, WHICHEVER IS GREATER.