


MATERIALS

FERRULE	CERAMIC
SLEEVE	CERAMIC
HOUSING	METAL



SPECIFICATIONS

Single Mode

PC Polish

Attenuation Value: 15dB $\pm$ 10% Typical, $\pm$ 15% Maximum

Operating Wavelength: 1300/1550 nm

Insertion Loss: <0.3dB Typical, 1dB Maximum

Return Loss: 40 dB Minimum, >50dB Typical

Operating Temperature: -40°C to +75°C



PASTERNAK ENTERPRISES, INC.

P.O BOX 16759, IRVINE, CA 92623
PHONE (949) 261-1920 FAX (949) 261-7451

WEB ADDRESS: www.pasternack.com
E-MAIL ADDRESS: sales@pasternack.com

COAXIAL & FIBER OPTICS

DWG TITLE

PE700001-15

DES. ST ATTENUATOR, SINGLE MODE

REV. B

FSCM NO. 53919

CAD FILE 050809

SCALE N/A

SIZE A

147

NOTES:

1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.
2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.
3. DIMENSIONS ARE IN INCHES.