



TECHNICAL DATA SHEET

PE15A3254 is a broadband GaAs PHEMT MMIC-based coaxial Low Noise Amplifier, operating in the 30 MHz to 20.0 GHz frequency range. The amplifier offers 3dB typical Noise Figure, 20 dBm of P1dB and 15dB small signal gain, with gain flatness of ±2.5 dB. This amplifier requires only a single positive DC supply with internal voltage regulation, is unconditionally stable, operates over the temperature range of -20°C to 70°C, and characterized by a light weight (11 g) and small size (1.08"x0.53"x0.29"). The rugged package is designed to meet series of MIL-STD-202F environmental conditions including humidity, shock, vibration, and temerature cycle, and features field removable SMA connectors for drop mounting onto a PWB.

Features

- 0.03 to 20 GHz Frequency Range
- P1dB: 20 dBm
- Small Signal Gain: 15 dB
- Gain Flatness: ±2.5 dB
- Noise Figure: 3 dB
- Output IP3: +29 dBm
- 50 Ohm Input and Output Matched

Applications

- Laboratory Applications
- R&D Labs
- Radar Systems
- Electronic Warfare
- Telecom Infrastructure
- Test Instrumentation

Satellite Communications

Wireless Communications

Communication Systems

Unmanned Systems

Military & Space

- Microwave Radio Systems
- Power Amplifier

-20 to +70°C Operating Temperature

Field Replaceable SMA Connectors

Built-in DC Voltage RegulatorSmall Size & Light Weight

Unconditionally Stable Single DC Positive Supply

- · Low Noise Amplifier
- · General Purpose Amplification
- RF Front Ends

Electrical Specifications (TA= 25°C)

Description	Minimum	Typical	Maximum	Units
Frequency Range	0.03		20	GHz
Gain		15		dB
Gain Flatness		±2.5		dB
Output at 1 dB Compression Point		+20		dBm
Output 3 rd Intercept Point		+29		dBm
Noise Figure		3		dB
Operating DC Voltage 1	12		15	Volts
Operating DC Current		180		mA
Operating Temperature Range (OTR)	-20		+70	°C

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: 3 dB NF, 20 dBm P1dB, 30 MHz to 20 GHz, Low Noise Broadband Amplifier, 15 dB Gain, SMA PE15A3254

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 Phone: (866) 727-8376 or (949) 261-1920 • Fax: (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com

PE15A3254



PE MARKE

PE15A3254

3 dB NF, 20 dBm P1dB, 30 MHz to 20 GHz, Low Noise Broadband Amplifier, 15 dB Gain, SMA

TECHNICAL DATA SHEET

Absolute Maximum Rating

Parameter Source Voltage	Rating +15	Units Volts
RF input Power	+23	dBm
Operating Temperature (base-plate)	-20 to +70	°C
Storage Temperature	-55 to +125	°C

ESD Sensitive Material, Transport material in Approved ESD bags. Handle only in approved ESD Workstation.

Mechanical Specifications

Size *Excluding Connectors* Length Width Height Weight

Connector Option Input Connector Output Connector

Environmental Specifications

Temperature Operating Range Storage Range

Humidity Shock

Altitude

1.08 in [27.43 mm] 0.36 in [9.14 mm] 0.18 in [4.57 mm] 0.0368 lbs [16.69 g]

Field Replaceable SMA Female SMA Female

-20 to +70 deg C -55 to +125 deg C

MIL-STD-202F, METHOD 103B COND B. MIL-STD-202F, METHOD 213B COND B. MIL-STD-202F, METHOD 105C COND B. MIL-STD-202F, METHOD 107D COND A.

Compliance Certifications (see product page for current document)

Plotted and Other Data

Temperature Cycling

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: 3 dB NF, 20 dBm P1dB, 30 MHz to 20 GHz, Low Noise Broadband Amplifier, 15 dB Gain, SMA PE15A3254

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 Phone: (866) 727-8376 or (949) 261-1920 • Fax: (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com



TECHNICAL DATA SHEET

PE15A3254

Typical Performance Data

Gain & Return Loss



Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: 3 dB NF, 20 dBm P1dB, 30 MHz to 20 GHz, Low Noise Broadband Amplifier, 15 dB Gain, SMA PE15A3254

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451 Sales@Pasternack.com • Techsupport@Pasternack.com



PE BASE

PE15A3254

3 dB NF, 20 dBm P1dB, 30 MHz to 20 GHz, Low Noise Broadband Amplifier, 15 dB Gain, SMA

TECHNICAL DATA SHEET



Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: 3 dB NF, 20 dBm P1dB, 30 MHz to 20 GHz, Low Noise Broadband Amplifier, 15 dB Gain, SMA PE15A3254

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com



NU PERMIT

PE15A3254

3 dB NF, 20 dBm P1dB, 30 MHz to 20 GHz, Low Noise Broadband Amplifier, 15 dB Gain, SMA

TECHNICAL DATA SHEET

Noise Figure Plot (500MHz to 20GHz)

Agilent 15:02:30 Jan 10, 2013 Frequency Freq Mode 16.648 dB 500 MHz 10 GHz 20 GHz Sweep Mkr2 Mkr3 14.360 dB 12.171 dB Start Fred 9.000 500.000000 MHz Stop Freq 20.0000000 GHz **Center Freq** NFI0 10.2500000 GHz Freq Span Ô 19.5000000 GHz Fixed Freq 14.7500000 GHz 1.000 More BW 4 MHz Stop 20.00000 GHz Start 500.00 MHz Points 20 1 of 2 Loss Off Tcold 296.90 K Avgs 3 Att 0/0 dB Corr ST01436.GIF file saved

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: 3 dB NF, 20 dBm P1dB, 30 MHz to 20 GHz, Low Noise Broadband Amplifier, 15 dB Gain, SMA PE15A3254

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com





TECHNICAL DATA SHEET

PE15A3254



OIP3 = Pout + dBc/2 +31.38dBm = 0 + (62.76/2)

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: 3 dB NF, 20 dBm P1dB, 30 MHz to 20 GHz, Low Noise Broadband Amplifier, 15 dB Gain, SMA PE15A3254

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 Phone: (866) 727-8376 or (949) 261-1920 • Fax: (949) 261-7451

 $Sales@Pasternack.com \ \bullet \ Techsupport@Pasternack.com$





TECHNICAL DATA SHEET

PE15A3254





Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: 3 dB NF, 20 dBm P1dB, 30 MHz to 20 GHz, Low Noise Broadband Amplifier, 15 dB Gain, SMA PE15A3254

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451 Sales@Pasternack.com • Techsupport@Pasternack.com

© 2019 Pasternack Enterprises All Rights Reserved





TECHNICAL DATA SHEET

PE15A3254

3 dB NF, 20 dBm P1dB, 30 MHz to 20 GHz, Low Noise Broadband Amplifier, 15 dB Gain, SMA from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: 3 dB NF, 20 dBm P1dB, 30 MHz to 20 GHz, Low Noise Broadband Amplifier, 15 dB Gain, SMA PE15A3254

URL: https://www.pasternack.com/3-db-20-ghz-low-noise-broadband-amplifier-15-db-gain-sma-pe15a3254-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451 Sales@Pasternack.com • Techsupport@Pasternack.com

PE15A3254 CAD Drawing

3 dB NF, 20 dBm P1dB, 30 MHz to 20 GHz, Low Noise



