



Low Loss 6 dB N Unequal Tapper Optimized For Mobile Networks From 380 MHz to 6 GHz Rated To 300 Watts

TECHNICAL DATA SHEET

PE-T2014

Low Loss 6 dB N Unequal Tapper Optimized For Mobile Networks From 380 MHz to 6 GHz Rated To 300 Watts

Pasternack's Line of High Power Wideband Tappers have been designed to maintain a Split Ratio across all frequencies between 380MHz and 6Ghz. There is minimal Insertion Loss, VSWR, and Low PIM. Mechanically the parts have no solder joints inside the Aluminum Casing and are IP65 / IP67 rated allowing for placement in rugged environments. This setup along with select bands optimization makes them ideal for Mobile Networks Infrastructure.

- Split Ratios Ranging from 1:3 to 1:1000
- · Power Ratings up to 300 Watts
- Low PIM (150dBc) Low VSWR (1.15)
- · Rugged Designs available with optional mounting brackets

Configuration

Design	Low Loss Tapper	
Frequency Range, GHz	0.38 to 6	
Input	N Female	
Output	N Female	
Sample Port	N Female	
Number of Output Ports	2	
Housing Material and Plating	Passivated Aluminum	

Electrical Specifications

Split Ratio	1:3
Number of Bands	4
Impedance, Ohms	50
Maximum Insertion Loss, dB *	1.47
Maximum Input Power, Watts	300
Maximum Input VSWR	1.5:1
Peak Input Power, KWatts	3
Passive Intermodulation (2 x 43 dBm), dBc	150

Band 1

Frequency, GHz	0.38 to 1.55
Coupling Tolerance, dB	0.75
VSWR	1.45

Band 2

Frequency, GHz	1.65 to 2.7
Coupling Tolerance, dB	0.75
VSWR	1.45:1

Band 3

Frequency, GHz	3.4 to 4.5
Coupling Tolerance, dB	1
VSWR	1.5:1

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: Low Loss 6 dB N Unequal Tapper Optimized For Mobile Networks From 380 MHz to 6 GHz Rated To 300 Watts PE-T2014

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal.

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623

Phone: (866) 727-8376 or (949) 261-1920 • Fax: (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com





Low Loss 6 dB N Unequal Tapper Optimized For Mobile Networks From 380 MHz to 6 GHz Rated To 300 Watts

TECHNICAL DATA SHEET

PE-T2014

_				
О	_	n	ᆈ	- 4

Range, GHz 5 to 6
Coupling Tolerance, dB 1.5
VSWR 1.45:1

Mechanical Specifications

Size

 Length, in [mm]
 6.23 [158.24]

 Width, in [mm]
 1 [25.4]

 Height, in [mm]
 2.1 [53.34]

 Weight, lbs [g]
 0.75 [340.19]

 Humidity
 IP65

Connector 1

Contact Material and Plating
Outer Conductor Material and Plating
Body Material and Plating
Brass, Tri-Metal
Brass, Tri-Metal
Brass, Tri-Metal

Connector 2

Contact Material and Plating

Outer Conductor Material and Plating

Brass, Tri-Metal

Brass, Tri-Metal

Brass, Tri-Metal

Brass, Tri-Metal

Brass, Tri-Metal

Connector 3

Contact Material and Plating

Outer Conductor Material and Plating

Brass, Tri-Metal

Brass, Tri-Metal

Brass, Tri-Metal

Brass, Tri-Metal

Brass, Tri-Metal

Compliance Certifications (visit www.Pasternack.com for current document)

RoHS Compliant Ye

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: Low Loss 6 dB N Unequal Tapper Optimized For Mobile Networks From 380 MHz to 6 GHz Rated To 300 Watts PE-T2014

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal.

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623

Phone: (866) 727-8376 or (949) 261-1920 • Fax: (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com





Low Loss 6 dB N Unequal Tapper Optimized For Mobile Networks From 380 MHz to 6 GHz Rated To 300 Watts

TECHNICAL DATA SHEET

PE-T2014

Plotted and Other Data

- * Notes: Values at 25 °C, sea level
 - Main line VSWR usable to DC
 - Coupling Port usable to 148 MHz or less with acceptable roll-off.
 - Insertion Loss = Dissipative Loss + Coupling Loss
 - · Resonant Free in listed operating bands, Resonance may occur outside specified operating bands

Low Loss 6 dB N Unequal Tapper Optimized For Mobile Networks From 380 MHz to 6 GHz Rated To 300 Watts from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and fiber optic products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: Low Loss 6 dB N Unequal Tapper Optimized For Mobile Networks From 380 MHz to 6 GHz Rated To 300 Watts PE-T2014

URL: http://www.pasternack.com/low-loss-6db-n-unequaltapper-380-mhz-6-ghz-300watts-pe-t2014-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal.

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 Phone: (866) 727-8376 or (949) 261-1920 • Fax: (949) 261-7451 Sales@Pasternack.com • Techsupport@Pasternack.com

PE-T2014 CAD Drawing

Low Loss 6 dB N Unequal Tapper Optimized For Mobile Networks From 380 MHz to 6 GHz Rated To 300 Watts

