

2 Way N Power Divider From 10 MHz to 1,000 MHz Rated at 1 Watt



# Power Dividers Technical Data Sheet PE2047 Features • 2-Way Power Divider • Max Power 1 Watt (CW) • Reactive Design • Insertion Loss < 1.5 dB</td> • 10 to 1,000 MHz Frequency Range • Isolation > 20 dB Applications • Commercial Communications • SATCOM • Military Communications • Wireless Communications • SATCOM

# Description

Pasternack carries a wide selection of power dividers to fit your needs. These components are essential in many systems, allowing the combination of multiple signals or splitting of a single signal into multiple signals with equal magnitude and phase. Pasternack's resistive and Wilkinson power dividers come with excellent performance featuring minimal loss, high isolation and low VSWR. They are available in both narrow and broad bandwidths with a variety of connector types such as 2.92mm, BNC, N and SMA.

The PE2047 is a 2-way reactive power divider that operates from 10 to 1,000 MHz and can handle up to 1 Watt (CW) with 1.5 dB max insertion loss and 20 dB min isolation. The package interface uses N female connectors and is REACH and RoHS compliant.

Reactive

2

### **Electrical Specifications**

Design

Number of Output Ports

Description	Minimum	Typical	Maximum	Units
Frequency Range	10		1,000	MHz
Impedance		50		Ohms
Input VSWR			1.5:1	
Output VSWR			1.5:1	
Insertion Loss			1.5	dB
Isolation	20			dB
Amplitude Balance			0.3	dB
Phase Balance			3	Degrees
Input Power (CW)			1	Watts

**Electrical Specification Notes:** 

Max input power rated for load VSWR better than 1.20:1.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: 2 Way N Power Divider From 10 MHz to 1,000 MHz Rated at 1 Watt PE2047

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 Phone: (866) 727-8376 or (949) 261-1920 • Fax: (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com



2 Way N Power Divider From 10 MHz to 1,000 MHz Rated at 1 Watt

**Power Dividers Technical Data Sheet** 

Mechanical Specifications

Size Lenath

Width

Height

Weight

Configuration Package Type

Input Connector

Temperature Operating Range

Storage Range

Humidity

Shock

Vibration

Altitude Thermal Shock

**Output Connectors** 

**Environmental Specifications** 



# © 2016 Pasternack Enterprises All Rights Reserved

Sales@Pasternack.com • Techsupport@Pasternack.com

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 Phone: (866) 727-8376 or (949) 261-1920 • Fax: (949) 261-7451





# PE2047

1.67 in [42.42 mm] 1.75 in [44.45 mm] 0.93 in [23.62 mm]

Connectorized N Female N Female

-25 to +80 deg C -55 to +150 deg C

MIL-STD-202, Method 106 (90% relative humidity, +65°C) MIL-STD-202, Method 213/I (100 G's, 6 ms) MIL-STD-202, Method 204/D (10 to 2,000 Hz, 20 G's, 12 hours) MIL-STD-202, Method 105/E (150,000 feet)

Compliance Certifications (visit www.Pasternack.com for current document)

**RoHS** Compliant **REACH** Compliant

12/17/2015

## **Plotted and Other Data**

Notes:

2 Way N Power Divider From 10 MHz to 1,000 MHz Rated at 1 Watt from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price. inventory and certifications: 2 Way N Power Divider From 10 MHz to 1,000 MHz Rated at 1 Watt PE2047

URL: http://www.pasternack.com/4-way-n-reactive-power-divider-10-mhz-1000-mhz-10-watts-pe2047-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

0.302 lbs [136.98 g]

MIL-STD-202, Method 107/B (-55°C to +85°C)

PE2047 CAD Drawing 2 Way N Power Divider From 10 MHz to 1,000 MHz Rated at 1 Watt

