

4 Way SMA Wilkinson Power Divider From 500 MHz to 1,000 MHz Rated at 30 Watts



#### **Power Dividers Technical Data Sheet PE2009 Features** 4-Way Power Divider Max Power 30 Watts (CW) High Power Wilkinson Design Insertion Loss < 0.4 dB • 500 to 1,000 MHz Frequency Range Isolation > 20 dB **Applications** Test and Measurement Commercial Communications SATCOM Military Communications Wireless Communications

## Description

Pasternack carries a wide selection of power dividers to fit your needs. These components are essential in many systems, allowing the combination of multiple signals or splitting of a single signal into multiple signals with equal magnitude and phase. Pasternack's resistive and Wilkinson power dividers come with excellent performance featuring minimal loss, high isolation and low VSWR. They are available in both narrow and broad bandwidths with a variety of connector types such as 2.92mm, BNC, N and SMA.

The PE2009 is a 4-way high power Wilkinson power divider that operates from 500 to 1,000 MHz and can handle up to 30 Watts (CW) with 0.4 dB max insertion loss and 20 dB min isolation. The package interface uses SMA female connectors and is REACH and RoHS compliant.

Wilkinson

4

### **Electrical Specifications**

Design

Number of Output Ports

Description	Minimum	Typical	Maximum	Units
Frequency Range	500		1,000	MHz
Impedance		50		Ohms
Input VSWR			1.3:1	
Output VSWR			1.3:1	
Insertion Loss			0.4	dB
Isolation	20			dB
Input Power (CW)			30	Watts

Electrical Specification Notes:

Max input power rated for load VSWR of 1.25:1 or better.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: 4 Way SMA Wilkinson Power Divider From 500 MHz to 1,000 MHz Rated at 30 Watts PE2009

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 Phone: (866) 727-8376 or (949) 261-1920 • Fax: (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com



4 Way SMA Wilkinson Power Divider From 500 MHz to 1,000 MHz Rated at 30 Watts





# **PE2009**

#### Mechanical Specifications Size Lenath 3 in [76.2 mm] Width 2.5 in [63.5 mm] Height 0.38 in [9.65 mm] Weight 0.233 lbs [105.69 g] Configuration Package Type Connectorized **SMA** Female Input Connector **SMA Female Output Connectors** Compliance Certifications (visit www.Pasternack.com for current document) **RoHS** Compliant **REACH** Compliant 12/17/2015

### Plotted and Other Data Notes:

4 Way SMA Wilkinson Power Divider From 500 MHz to 1,000 MHz Rated at 30 Watts from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: 4 Way SMA Wilkinson Power Divider From 500 MHz to 1,000 MHz Rated at 30 Watts PE2009

URL: http://www.pasternack.com/4-way-sma-reactive-power-divider-500-mhz-1000-mhz-10-watts-pe2009-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 Phone: (866) 727-8376 or (949) 261-1920 • Fax: (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com

# PE2009 CAD Drawing

4 Way SMA Wilkinson Power Divider From 500 MHz to 1,000 MHz Rated at 30 Watts

