

N Male to N Male Low Loss Test Cable 100 CM Length Using PE-P300LL Coax, RoHS



# **RF Cable Assemblies Technical Data Sheet**


### PE330-100CM

### Configuration

- Connector 1: N Male
- Connector 2: N Male
- Cable Type: PE-P300LL

### Features

- 83% Velocity of Propagation
- Shielding effectiveness > 95 dB
- Maximum VSWR is < 1.35:1 to 18 GHz
- Minimum Bend Radius of 1.5 inches
- Operating Temperature range of -55 to +125 °C
- ROHS and REACH Compliant
- · Same day shipment of custom lengths
- 100% Continuity and RF tested



### Description

The PE330 high performance test cable's 0.3 inch diameter and 83% phase velocity offer very low loss performance up to 18 GHz. The durable stainless steel connectors and FEP jacket provide a cost effective design ideal for test environments where a rugged cable assembly is required. The series is offered with Type N, TNC, and SMA connectors all rated to 18 GHz. A heavy Duty boot provides improved strain relief and adds to the durability of the cable assemblies. These cable assemblies are built using a double shielded flexible cable, providing excellent shielding effectiveness of greater than 95 dB. All PE330 cable assemblies are 100% Continuity and RF tested to published specifications. Custom lengths are built to order and shipped same day.

### **Electrical Specifications**

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		18	GHz
VSWR			1.35:1	
Velocity of Propagation		83		%
RF Shielding	95			dB
Capacitance		25 [82.02]		pF/ft [pF/m]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: N Male to N Male Low Loss Test Cable 100 CM Length Using PE-P300LL Coax, RoHS PE330-100CM

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 Phone: (866) 727-8376 or (949) 261-1920 • Fax: (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com



N Male to N Male Low Loss Test Cable 100 CM Length Using PE-P300LL Coax, RoHS

# **RF Cable Assemblies Technical Data Sheet**



### PE330-100CM

#### **Specifications by Frequency**

Description	F1	F2	F3	F4	F5	Units
Frequency	1	2	4.5	9	18	GHz
Insertion Loss (Max.)	0.4	0.46	0.58	0.78	1.03	dB
Insertion Loss (Typ.)	0.36	0.42	0.52	0.68	0.9	dB
Power Handling (Max.)	1,800	1,200	900	650	400	Watts

#### Mechanical Specifications

Cable Assembly Length\* Diameter

#### Cable

Cable Type Impedance Inner Conductor Type Inner Conductor Material and Plating Dielectric Type Number of Shields Shield Layer 1 Shield Layer 2 Shield Layer 3 Outer Conductor Material and Plating Jacket Material Jacket Diameter

Repeated Minimum Bend Radius

39.37 in [100 cm] 0.75 in [19.05 mm]

PE-P300LL 50 Ohms Solid Copper, Silver PTFE 3 Silver Plated Copper Tape Aluminum Polyester Silver Plated Copper Wire Copper, Silver FEP, Green 0.3 in [7.62 mm]


1.5 in [38.1 mm]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: N Male to N Male Low Loss Test Cable 100 CM Length Using PE-P300LL Coax, RoHS PE330-100CM

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 Phone: (866) 727-8376 or (949) 261-1920 • Fax: (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com





### **RF Cable Assemblies Technical Data Sheet**

# PE330-100CM

Harman Harman

#### Connectors

Description	Connector 1	Connector 2 N Male	
Туре	N Male		
Impedance	50 Ohms	50 Ohms	
Mating Cycles	500	500	
Contact Material and Plating	Beryllium Copper, Gold	Beryllium Copper, Gold	
Contact Plating Specification	ASTM-B488 50µ In.	ASTM-B488 50µ In.	
Dielectric Type	PTFE	PTFE	
Outer Conductor Material and Plating	Passivated Stainless Steel	Passivated Stainless Steel	
Outer Conductor Plating Specification	SAE-AMS-2700	SAE-AMS-2700	
Body Material and Plating	Passivated Stainless Steel	Passivated Stainless Steel	
Body Plating Specification	SAE-AMS-2700	SAE-AMS-2700	
Coupling Nut Material and Plating	Passivated Stainless Steel	Passivated Stainless Steel	
Coupling Nut Plating Specification	SAE-AMS-2700	SAE-AMS-2700	
Hex Size	3/4 Inch 3/4 Inc		
Torque	14 in-lbs [1.58 Nm]	14 in-lbs [1.58 Nm]	

Mechanical Specification Notes:

\*All cable assemblies have a length tolerance of 1.5% or  $\pm$  3/8", whichever is greater.

#### **Environmental Specifications**

Temperature Operating Range

-55 to +125 deg C

Compliance Certifications (see product page for current document)

### Plotted and Other Data

Notes:

• Values at 25°C, sea level.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: N Male to N Male Low Loss Test Cable 100 CM Length Using PE-P300LL Coax, RoHS PE330-100CM

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 Phone: (866) 727-8376 or (949) 261-1920 • Fax: (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com




C THISTORY HISTORY

## N Male to N Male Low Loss Test Cable 100 CM Length Using PE-P300LL Coax, RoHS

# **RF Cable Assemblies Technical Data Sheet**

### PE330-100CM



Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451 **Sales@Pasternack.com** • Techsupport@Pasternack.com

© 2017 Pasternack Enterprises All Rights Reserved

PE330-100CM CAD Drawing N Male to N Male Low Loss Test Cable 100 CM Length Using PE-P300LL Coax, RoHS

