



## **RF Cable Assemblies Technical Data Sheet**


PE332-12

# Configuration

Connector 1: N MaleConnector 2: SMA MaleCable Type: PE-P300LL

### **Features**

- 83% Velocity of Propagation
- Shielding effectiveness > 95 dB
- Maximum VSWR is < 1.35:1 to 18 GHz
- · Minimum Bend Radius of 1.5 inches
- Operating Temperature range of -55 to +125 °C
- ROHS and REACH Compliant
- Same day shipment of custom lengths
- 100% Continuity and RF tested



### Description

The PE330 high performance test cable's 0.3 inch diameter and 83% phase velocity offer very low loss performance up to 18 GHz. The durable stainless steel connectors and FEP jacket provide a cost effective design ideal for test environments where a rugged cable assembly is required. The series is offered with Type N, TNC, and SMA connectors all rated to 18 GHz. A heavy Duty boot provides improved strain relief and adds to the durability of the cable assemblies. These cable assemblies are built using a double shielded flexible cable, providing excellent shielding effectiveness of greater than 95 dB. All PE330 cable assemblies are 100% Continuity and RF tested to published specifications. Custom lengths are built to order and shipped same day.

#### **Electrical Specifications**

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		18	GHz
VSWR			1.35:1	
Velocity of Propagation		83		%
RF Shielding	95			dB
Capacitance		25 [82.02]		pF/ft [pF/m]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: N Male to SMA Male Low Loss Test Cable 12 Inch Length Using PE-P300LL Coax, RoHS PE332-12

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com





## **RF Cable Assemblies Technical Data Sheet**

PE332-12

#### Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	1	2	4.5	9	18	GHz
Insertion Loss (Max.)	0.26	0.28	0.32	0.38	0.46	dB
Insertion Loss (Typ.)	0.25	0.27	0.3	0.35	0.42	dB
Power Handling (Max.)	1,800	1,200	900	650	400	Watts

## **Mechanical Specifications**

**Cable Assembly** 

Length\* 12 in [304.8 mm]
Diameter 0.75 in [19.05 mm]

Cable

Cable Type PE-P300LL
Impedance 50 Ohms
Inner Conductor Type Solid
Inner Conductor Material and Plating Copper, Silv

Inner Conductor Material and Plating Copper, Silver Dielectric Type PTFE

Number of Shields 3
Shield Layer 1 Silver Plated Copper Tape
Shield Layer 2 Aluminum Polyester

Shield Layer 3 Silver Plated Copper Wire Outer Conductor Material and Plating Copper, Silver

Jacket Diameter 0.3 in [7.62 mm]

Repeated Minimum Bend Radius 1.5 in [38.1 mm]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: N Male to SMA Male Low Loss Test Cable 12 Inch Length Using PE-P300LL Coax, RoHS PE332-12

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451





## **RF Cable Assemblies Technical Data Sheet**

PE332-12

#### Connectors

Description	Connector 1	Connector 2	
Туре	N Male	SMA Male	
Specification		MIL-STD-348	
Impedance	50 Ohms	50 Ohms	
Mating Cycles	500	500	
Contact Material and Plating	Beryllium Copper, Gold	Beryllium Copper, Gold	
Contact Plating Specification	ASTM-B488 50μ In.	ASTM-B488 50μ In.	
Dielectric Type	PTFE	PTFE	
Outer Conductor Material and Plating	Passivated Stainless Steel	Passivated Stainless Steel	
Outer Conductor Plating Specification	SAE-AMS-2700	SAE-AMS-2700	
Body Material and Plating	Passivated Stainless Steel	Passivated Stainless Steel	
Body Plating Specification	SAE-AMS-2700	SAE-AMS-2700	
Coupling Nut Material and Plating	Passivated Stainless Steel	Passivated Stainless Steel	
Coupling Nut Plating Specification	SAE-AMS-2700	SAE-AMS-2700	
Hex Size	3/4 Inch	5/16 Inch	
Torque	14 in-lbs [1.58 Nm]	8 in-lbs [0.9 Nm]	

Mechanical Specification Notes:

## **Environmental Specifications**

Temperature

**Operating Range** 

-55 to +125 deg C

Compliance Certifications (see product page for current document)

### **Plotted and Other Data**

Notes:

• Values at 25°C, sea level.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: N Male to SMA Male Low Loss Test Cable 12 Inch Length Using PE-P300LL Coax, RoHS PE332-12

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com

<sup>\*</sup>All cable assemblies have a length tolerance of 1.5% or ± 3/8", whichever is greater.





## **RF Cable Assemblies Technical Data Sheet**

PE332-12

#### **How to Order**



Example: PE332-12 = 12 inches long cable

PE332-100cm = 100 cm long cable

N Male to SMA Male Low Loss Test Cable 12 Inch Length Using PE-P300LL Coax, RoHS from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: N Male to SMA Male Low Loss Test Cable 12 Inch Length Using PE-P300LL Coax, RoHS PE332-12

URL: https://www.pasternack.com/n-male-sma-male-pe-p300ll-cable-assembly-pe332-12-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623

Phone: (866) 727-8376 or (949) 261-1920 • Fax: (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com

