

SMA Male to SMA Female Bulkhead Semi-Flexible Cable Using PE-SR405FL Coax



PE39419


RF Cable Assemblies Technical Data Sheet

Configuration

- Connector 1: SMA Male
- Connector 2: SMA Female Bulkhead
- Cable Type: PE-SR405FL

Features

- Dimensionally and electrically the same as standard, solid outer conductor semi-rigid coax
- Cable may be formed by hand and does not require special tools to bend
- May be formed more than once without damaging the outer conductor
- High RF Shielding >100 dB
- 100% Hi-pot and continuity tested
- 100% VSWR tested to max frequency of assembly
- · Standard and custom lengths ship the same day



Description

Pasternack's formable cable assemblies are hand formable semi-rigid replacements that are an alternative to costly preformed assemblies. The formable semi-rigid cable alternatives are dimensionally and electrically similar to their semi-rigid counterpart and have a tinned-copper-braid outer shield that provides excellent RF shielding. The hand formable cable assemblies from Pasternack do not require special tooling to shape or reshape the assemblies and can replace standard semi-rigid versions. The assemblies are available with or without a FEP jacket and are RoHS compliant,

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		18	GHz
VSWR			1.5:1	
Velocity of Propagation		69.5		%
Capacitance		29 [95.14]		pF/ft [pF/m]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: SMA Male to SMA Female Bulkhead Semi-Flexible Cable Using PE-SR405FL Coax PE39419

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 Phone: (866) 727-8376 or (949) 261-1920 • Fax: (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com



SMA Male to SMA Female Bulkhead Semi-Flexible Cable Using PE-SR405FL Coax

RF Cable Assemblies Technical Data Sheet



PE39419

Description	F1	F2	F3	F4	F5	Units
Frequency	1	2	4.5	9	18	GHz
						dB/m
Insertion Loss (Typ.)	0.425	0.506	0.709	0.959	1.322	dB/ft
	1.39	1.66	2.33	3.15	4.34	dB/m
hanical Specificatio	ns					
Cable Assembly						
Diamatan						
Diameter			0.	433 in [11 mn	n]	
				433 in [11 mn 022 lbs [9.98	-	
Weight					-	
Weight Cable			0.		-	
Weight Cable Cable Type			0. P	022 lbs [9.98	-	
Weight Cable Cable Type Impedance			0. P 50	022 lbs [9.98 E-SR405FL	-	
Weight Cable Cable Type Impedance Inner Conductor Type Inner Conductor Materia	al and Plating		0. P 50 S	022 lbs [9.98 E-SR405FL) Ohms	a]	
Weight Cable Cable Type Impedance Inner Conductor Type Inner Conductor Materia Dielectric Type	I and Plating		0. P 5(S C	022 lbs [9.98 E-SR405FL) Ohms olid	a]	
Weight Cable Cable Type Impedance Inner Conductor Type Inner Conductor Materia Dielectric Type Number of Shields			0. P 50 S C P 1	022 lbs [9.98 E-SR405FL O Ohms olid opper Clad St TFE	g] teel, Silver	
Diameter Weight Cable Cable Type Impedance Inner Conductor Type Inner Conductor Materia Dielectric Type Number of Shields Outer Conductor Diame			0. P 50 S C P 1	022 lbs [9.98 E-SR405FL 0 Ohms olid opper Clad St	g] teel, Silver	

Connectors

Connector 1	Connector 2		
SMA Male	SMA Female Bulkhead		
50 Ohms	50 Ohms		
Brass, Gold over Nickel	Beryllium Copper, Gold over Nickel		
PTFE	PTFE		
Brass, Gold over Nickel	Brass, Gold over Nickel		
Passivated Stainless Steel			
5/16 inch			
8 in-lbs [0.9 Nm]			
	SMA Male 50 Ohms Brass, Gold over Nickel PTFE Brass, Gold over Nickel Passivated Stainless Steel 5/16 inch		

Mechanical Specification Notes:

*All cable assemblies have a length tolerance of 1.5% or $\pm 3/8$ ", whichever is greater.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: SMA Male to SMA Female Bulkhead Semi-Flexible Cable Using PE-SR405FL Coax PE39419

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 Phone: (866) 727-8376 or (949) 261-1920 • Fax: (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com



SMA Male to SMA Female Bulkhead Semi-Flexible Cable Using PE-SR405FL Coax

RF Cable Assem	blies Technical I	Data Sheet		PE39419
Tempe	ental Specifications erature ting Range	-65	to +125 deg C	
Complian	ce Certifications (see prod	uct page for current document)	
Plotted a Notes:	nd Other Data			
How to O	rder			
Part N	umber Configuration:	PE39419	- xx uu	
				 Unit of Measure: cm = Centimeters <blank> = Inches</blank> Length Base Number
Examp	ble: PE39419-12 = 12 inche PE39419-100cm = 100			

SMA Male to SMA Female Bulkhead Semi-Flexible Cable Using PE-SR405FL Coax from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: SMA Male to SMA Female Bulkhead Semi-Flexible Cable Using PE-SR405FL Coax PE39419

URL: https://www.pasternack.com/sma-male-sma-female-pe-sr405fl-cable-assembly-pe39419-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451 Sales@Pasternack.com • Techsupport@Pasternack.com

0



PE39419 CAD Drawing SMA Male to SMA Female Bulkhead Semi-Flexible Cable Using PE-SR405FL Coax

