

TNC Male to TNC Male Low Loss Test Cable 60 Inch Length Using PE-P300LL Coax, RoHS



RF Cable Assemblies Technical Data Sheet


PE334-60

Configuration

Connector 1: TNC MaleConnector 2: TNC MaleCable Type: PE-P300LL

Features

- 83% Velocity of Propagation
- Shielding effectiveness > 95 dB
- Maximum VSWR is < 1.35:1 to 18 GHz
- · Minimum Bend Radius of 1.5 inches
- Operating Temperature range of -55 to +125 °C
- · ROHS and REACH Compliant
- · Same day shipment of custom lengths
- 100% Continuity, Hi-Pot, and RF tested



Description

The PE330 high performance test cable's 0.3 inch diameter and 83% phase velocity offer very low loss performance up to 18 GHz. The durable stainless steel connectors and FEP jacket provide a cost effective design ideal for test environments where a rugged cable assembly is required. The series is offered with Type N, TNC, and SMA connectors all rated to 18 GHz. A heavy Duty boot provides improved strain relief and adds to the durability of the cable assemblies. These cable assemblies are built using a double shielded flexible cable, providing excellent shielding effectiveness of greater than 95 dB. All PE330 cable assemblies are 100% Continuity, Hi-POT, and RF tested to published specifications. Custom lengths are built to order and shipped same day.

Electrical Specifications

•				
Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		18	GHz
VSWR			1.35:1	
Velocity of Propagation		83		%
RF Shielding	95			dB
Capacitance		25 [82.02]		pF/ft [pF/m]

Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	1	2	4.5	9	18	GHz
Power Handling (Max.)	2,900	1,350	900	650	400	Watts

Electrical Specification Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: TNC Male to TNC Male Low Loss Test Cable 60 Inch Length Using PE-P300LL Coax, RoHS PE334-60

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com



TNC Male to TNC Male Low Loss Test Cable 60 Inch Length Using PE-P300LL Coax, RoHS



RF Cable Assemblies Technical Data Sheet

PE334-60

Power handling values are calculated based on Cable properties. Power handling will vary based on the actual VSWR of the cable assembly.

Mechanical Specifications

Cable Assembly

Length* Diameter 60 in [152.4 cm] 0.625 in [15.88 mm]

Cable

Cable Type Impedance

Inner Conductor Type

Inner Conductor Material and Plating

Dielectric Type Number of Shields Shield Layer 1 Shield Layer 2 Shield Layer 3

Outer Conductor Material and Plating

Jacket Material Jacket Diameter

cket Material

Repeated Minimum Bend Radius

PE-P300LL 50 Ohms Solid

Copper, Silver

PTFE 3

> Silver Plated Copper Tape Aluminum Polyester Silver Plated Copper Wire

Copper, Silver FEP, Green 0.3 in [7.62 mm]

1.5 in [38.1 mm]

Connectors

Description	Connector 1	Connector 2 TNC Male		
Туре	TNC Male			
Specification	MIL-STD-348	MIL-STD-348		
Impedance	50 Ohms	50 Ohms		
Contact Material and Plating	Beryllium Copper, Gold	Beryllium Copper, Gold		
Contact Plating Specification	ASTM-B488 50μ In.	ASTM-B488 50μ ln.		
Dielectric Type	PTFE	PTFE		
Outer Conductor Material and Plating	Passivated Stainless Steel	Passivated Stainless Steel		
Outer Conductor Plating Specification	SAE-AMS-2701	SAE-AMS-2701		
Body Material and Plating	Passivated Stainless Steel	Passivated Stainless Steel		
Body Plating Specification	SAE-AMS-2701	SAE-AMS-2701		
Coupling Nut Material and Plating	Passivated Stainless Steel	Passivated Stainless Steel		
Coupling Nut Plating Specification	SAE-AMS-2701	SAE-AMS-2701		
Hex Size	9/16 Inch	9/16 Inch		
Torque	14 in-lbs [1.58 Nm]	14 in-lbs [1.58 Nm]		

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: TNC Male to TNC Male Low Loss Test Cable 60 Inch Length Using PE-P300LL Coax, RoHS PE334-60

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com



TNC Male to TNC Male Low Loss Test Cable 60 Inch Length Using PE-P300LL Coax, RoHS



RF Cable Assemblies Technical Data Sheet

PE334-60

Mechanical Specification Notes:

*All cable assemblies have a length tolerance of 1.5% or ± 3/8", whichever is greater.

Environmental Specifications

Temperature

Operating Range -55 to +125 deg C

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

• Values at 25°C, sea level.

How to Order

Part Number Configuration:

PE334 - xx uu

Unit of Measure:
cm = Centimeters

clank> = Inches

Length

Base Number

Example: PE334-12 = 12 inches long cable PE334-100cm = 100 cm long cable

TNC Male to TNC Male Low Loss Test Cable 60 Inch Length Using PE-P300LL Coax, RoHS from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: TNC Male to TNC Male Low Loss Test Cable 60 Inch Length Using PE-P300LL Coax, RoHS PE334-60

URL: https://www.pasternack.com/tnc-male-tnc-male-pe-p300ll-cable-assembly-pe334-60-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451

PE334-60 CAD DrawingTNC Male to TNC Male Low Loss Test Cable 60 Inch Length Using PE-P300LL Coax, RoHS

