


COMPONENTS	IMPEDANCE
BNC MALE	75 OHM
BNC MALE	75 OHM
PE-B159	75 OHM

Part Configurator	
1. Replace ZZ with color codes.	
2. Replace XX with length in inches.	
Standard Lengths	
-12	12"
-24	24"
-36	36"
-48	48"
-60	60"
-XXX	Custom Length in inches

Color Codes	
BK	Black
BL	Blue
GR	Green
RD	Red
WH	White
YW	Yellow



**PASTERNACK ENTERPRISES, INC.**  
P.O BOX 16759, IRVINE, CA 92623  
PHONE (949) 261-1920 FAX (949) 261-7451  
WEB ADDRESS: [www.pasternack.com](http://www.pasternack.com)  
E-MAIL ADDRESS: [sales@pasternack.com](mailto:sales@pasternack.com)  
**COAXIAL & FIBER OPTICS**

DWG TITLE	DES.
<b>PE38130/ZZ-XX</b>	CABLE ASSEMBLY, PE-B159, 75 OHM HD PRECISION, BNC MALE TO BNC MALE

REV. C	FSCM NO. 53919	CAD FILE 082411	SCALE N/A	SIZE A	2231
--------	----------------	-----------------	-----------	--------	------

**NOTES:**  
1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.  
2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.  
3. DIMENSIONS ARE IN INCHES [mm].  
4. LENGTH TOLERANCE IS  $\pm 1.5\%$  OR 3/8, WHICHEVER IS GREATER.