

# N Male to N Male Low Loss Cable 60 Inch Length Using PE-P142LL Coax with HeatShrink



### RF Cable Assemblies Technical Data Sheet

PE3C0231-60

## Configuration

· Connector 1: N Male · Connector 2: N Male Cable Type: PE-P142LL


#### **Features**

- Passivated Stainless Steel Flexible Armoring
- Type N Male to N Male and SMA Male to SMA Male Configurations Available
- Robust Connector/Armor Interface
- · Triple Shielded Low Loss PE-P142LL Coax with Expanded PTFE Tape Dielectric
- Standard inch lengths: 24", 36", 48", 60", 72", 120"
- Standard metric lengths: 50cm, 100cm, 150cm, 200cm
- SMA rated to 20 GHz with a 1.35:1 VSWR
- N type rated to 18 GHz with a 1.35:1 VSWR
- · Custom lengths available, call for pricing and lead time

# **Applications**

General Purpose

· Laboratory Use



#### Description

Pasternack's new SMA and type N armored test cables utilize a flexible passivated stainless steel armoring that is designed to handle harsh industrial environments, common in production test systems. Its rugged armoring is very flexible and ensures RF signal integrity during test, even when exposed to a high traffic production environment. These armored RF test cables are equipped with passivated stainless steel connectors, with the SMA designed to operate to 20 GHz and the type N to 18 GHz. A robust mechanical connector/armoring interface increases the durability of the test cables, and its strain relief boot increases the life of the test cable. Pasternack's armored test cables are built using PE-P142LL coaxial cable that is triple shielded with an expanded PTFE dielectric, guaranteeing low loss performance.

### **Electrical Specifications**

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		18	GHz
VSWR		1.25:1	1.35:1	
Velocity of Propagation		80		%

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: N Male to N Male Low Loss Cable 60 Inch Length Using PE-P142LL Coax with HeatShrink PE3C0231-60

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 Phone: (866) 727-8376 or (949) 261-1920 • Fax: (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com



# N Male to N Male Low Loss Cable 60 Inch Length Using PE-P142LL Coax with HeatShrink



#### RF Cable Assemblies Technical Data Sheet

#### PE3C0231-60

#### **Specifications by Frequency**

Description	F1	F2	F3	F4	F5	Units
Frequency	1	3	5	10	18	GHz
Insertion Loss (Typ.)	0.4	0.7	0.9	1.25	1.8	dB
Power Handling (Max.)				220		Watts

**Electrical Specification Notes:** 

Insertion loss does not include the loss of the connectors.

Insertion loss is estimated as 0.05 x sqrt(fGHz) dB per connector.

#### **Mechanical Specifications**

Cable Assembly

Length\* 60 in [152.4 cm]

Weight 0.73 lbs [331.12 g]

Cable

Cable Type PE-P142LL Impedance 50 Ohms Inner Conductor Type Solid

Inner Conductor Material and Plating Copper, Silver Dielectric Type PTFE

Dielectric Type
Number of Shields
3
Shield Layer 1
Silver Plated Copper Braid
Shield Layer 2
Shield Layer 3
Jacket Material
Jacket Diameter
PTFE
Aluminum Polyester
Silver Plated Copper Braid
Passivated Copper Braid
Passivated Stainless Steel
0.32 in [8.13 mm]

Repeated Minimum Bend Radius 1 in [25.4 mm]

#### Connectors

Description	Connector 1	Connector 2		
Туре	N Male	N Male		
Impedance	50 Ohms	50 Ohms		
Contact Material and Plating	Brass, Gold	Brass, Gold		
Body Material and Plating	Passivated Stainless Steel	Passivated Stainless Steel		
Coupling Nut Material and Plating	Passivated Stainless Steel	Passivated Stainless Steel		

Mechanical Specification Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: N Male to N Male Low Loss Cable 60 Inch Length Using PE-P142LL Coax with HeatShrink PE3C0231-60

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com



# N Male to N Male Low Loss Cable 60 Inch Length Using PE-P142LL Coax with HeatShrink



#### **RF Cable Assemblies Technical Data Sheet**

PE3C0231-60

\*All cable assemblies have a length tolerance of 1.5% or  $\pm$  3/8", whichever is greater.

#### **Environmental Specifications**

**Temperature** 

Operating Range

-55 to +200 deg C

Compliance Certifications (see product page for current document)

#### **Plotted and Other Data**

Notes:

• Values at 25°C, sea level.

#### How to Order

Part Number Configuration:

PE3C0231 - xx uu

Unit of Measure:
cm = Centimeters
<br/>
<br/>
<br/>
clanck > = Inches
<br/>
Length
<br/>
Base Number

Example: PE3C0231-12 = 12 inches long cable

PE3C0231-100cm = 100 cm long cable

N Male to N Male Low Loss Cable 60 Inch Length Using PE-P142LL Coax with HeatShrink from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: N Male to N Male Low Loss Cable 60 Inch Length Using PE-P142LL Coax with HeatShrink PE3C0231-60

URL: https://www.pasternack.com/n-male-n-male-pe-p142ll-cable-assembly-pe3c0231-60-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 Phone: (866) 727-8376 or (949) 261-1920 • Fax: (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com

PE3C0231-60 CAD Drawing
N Male to N Male Low Loss Cable 60 Inch Length Using PE-P142LL Coax with HeatShrink

