

High Power 100 Watt RF Load Up to 3 GHz With 7/16 DIN Male Input Conduction Cooled Body Black Anodized Aluminum Heatsink



PE6197

RF Terminations Technical Data Sheet

Features

- High Power RF Load
- DC to 3 GHz Frequency Range
- VSWR 1.2:1 Max

Applications

- Wireless
- SatCom

- Radar Systems
- Test and Measurement
- Commercial and Military
 Communication

Max Power 100 Watt (CW)

7/16 DIN Male Coaxial Interface

Description

Pasternack's PE6197 is a high power RF termination (also called RF load or dummy load) that operates from DC to 3 GHz and handles up to 100 Watt (CW). Our 7/16 DIN termination / load has a male gender. PE6197 7/16 DIN load termination offers 1.2:1 max VSWR. This Pasternack high power 100W 7/16 DIN terminator has a heatsink body which is designed to provide adequate heat dissipation within its full frequency of operation.

RF load / terminations are indispensable components in many RF, microwave and millimeter wave systems where signal reflection from unused ports can potentially damage the device or reduce the signal integrity. By using a terminator on an unused port with a matched load (dummy load), the incident energy will be absorbed with minimal reflection. These termination components are commonly used to terminate devices such as couplers, circulators, and switches. They are also widely used in measurement systems to ensure accurate results. Pasternack offers a huge selection of RF, microwave and millimeter wave terminations up to 65 GHz with excellent performance over the entire operating range and power handling capabilities up to 800 Watt (CW).

Electrical Specifications

Description		Minimur	n Typical	Maximum	Units
Frequency Range		DC		3	GHz
Impedance			50		Ohms
VSWR				1.2:1	
Input Power (CW)				100	Watts
derated linearly to 20W	/ at +125°C				

Mechanical Specifications

Size	
Length	6.3 in [160.02 mm]
Width	4.72 in [119.89 mm]
Height	3.54 in [89.92 mm]
Weight	3.36 lbs [1.52 Kg]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: High Power 100 Watt RF Load Up to 3 GHz With 7/16 DIN Male Input Conduction Cooled Body Black Anodized Aluminum Heatsink PE6197

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 Phone: (866) 727-8376 or (949) 261-1920 • Fax: (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com



High Power 100 Watt RF Load Up to 3 GHz With 7/16 DIN Male Input Conduction Cooled Body Black Anodized Aluminum Heatsink



PE6197

RF Terminations Technical Data Sheet

Configuration Connector 7/16 DIN Male Hex Size 32 mm Material Specifications Material Description Plating Connector 1 Contact Brass Silver PTFE Insulation Body Brass Tri-Metal Coupling Nut Brass Tri-Metal Black Anodized Aluminum Heatsink Housing **Environmental Specifications** Temperature **Operating Range** -45 to +125 deg C Compliance Certifications (visit www.Pasternack.com for current document) **RoHS** Compliant **REACH Compliant** 12/17/2015 Plotted and Other Data Notes: High Power 100 Watt RF Load Up to 3 GHz With 7/16 DIN Male Input Conduction Cooled Body Black Anodized Aluminum Heatsink from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry. Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: High Power 100 Watt RF Load Up to 3 GHz With 7/16 DIN Male Input Conduction Cooled Body Black Anodized Aluminum Heatsink PE6197 URL: http://www.pasternack.com/100-watts-7-16-male-rf-load-up-to-3-ghz-pe6197-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 Phone: (866) 727-8376 or (949) 261-1920 • Fax: (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com

PE6197 CAD Drawing High Power 100 Watt RF Load Up to 3 GHz With 7/16 DIN Male Input

Conduction Cooled Body Black Anodized Aluminum Heatsink

32mm HEX NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm]. 3045 ∢ 1.13 [28.6] REF. SIZE PEmin LABEL: PE6197 Т SCALE N/A \oplus \oplus \oplus \oplus 060816 CAD FILE 6.30 [160.0] \oplus \oplus 53919 \oplus Ð Ś **PE6197** FSCM DWG TITLE \oplus \bigcirc 4.73 [120.1] Website: www.pasternack.com | E-Mail: sales@pasternack.com 1.18 [30.0] Phone: (949) 261-1920 | Fax: (949) 261-7451 7/16 DIN MALE Pasternack Enterprises, Inc. P.O. Box 16759 | Irvine | CA | 92623 PASTERNACK THE ENGINEER'S RF SOURCE 3.54 [90.0] (0) 1.18 [30.0] *STANDARD TOLERANCES APPLY ONLY TO DIMENSIONS IN INCHES Π STANDARD TOLERANCES ±0.20 ±0.10 DECIMAL ××