



RF Cable Assemblies Technical Data Sheet

PE3C5030

Configuration

· Connector 1: N Female Bulkhead

• Connector 2: SMA Male Reverse Polarity Right Angle

Cable Type: RG400

Features

- Max Frequency 6 GHz
- 70% Phase Velocity
- · Double Shielded
- FEP Jacket

Applications

General Purpose

· Laboratory Use

Description

Pasternack's PE3C5030 type N female bulkhead to reverse polarity SMA male right angle cable using RG400 coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack type N to reverse polarity SMA cable assembly has a female to male gender configuration with 50 ohm flexible RG400 coax. The PE3C5030 type N female to reverse polarity SMA male cable assembly operates to 6 GHz. The right angle SMA interface on the RG400 cable allows for easier connections in tight spaces. Our RF cable assembly with type N bulkhead interface allows designers to create external connections on their product enclosures, and can be used in a variety of other rack mount and panel mount applications. The double shielding of this Pasternack cable assembly provides excellent shielding effectiveness.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		6	GHz
VSWR			1.5:1	
Velocity of Propagation		70		%
Capacitance		32 [104.99]		pF/ft [pF/m]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: N Female Bulkhead to Reverse Polarity SMA Male Right Angle Cable Using RG400 Coax PE3C5030

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com





RF Cable Assemblies Technical Data Sheet

PE3C5030

Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	0.25	0.5	1	2.5	6	GHz
Insertion Loss (Typ.)	0.07	0.1	0.15	0.24	0.4	dB/ft
	0.23	0.33	0.49	0.79	1.31	dB/m

Electrical Specification Notes:

Insertion Loss does not include the loss of the connectors. Insertion Loss is estimated as 0.3dB of connector loss.

Mechanical Specifications

Cable Assembly

Diameter 0.827 in [21.01 mm]

Cable

Cable Type Impedance

Inner Conductor Type

Inner Conductor Material and Plating

Dielectric Type Number of Shields Shield Layer 1 Shield Layer 2

Jacket Material Jacket Diameter

Repeated Minimum Bend Radius

RG400 50 Ohms Stranded

Copper, Silver PTFE

2

Silver Plated Copper Braid Silver Plated Copper Braid

FEP, Tan

0.195 in [4.95 mm]

1 in [25.4 mm]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: N Female Bulkhead to Reverse Polarity SMA Male Right Angle Cable Using RG400 Coax PE3C5030

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451





RF Cable Assemblies Technical Data Sheet

PE3C5030

Connectors

Description	Connector 1 Connector 2			
Туре	N Female Bulkhead	SMA Male Reverse Polarity Right Angl		
Specification	MIL-STD-348A			
Impedance	50 Ohms	50 Ohms		
Contact Material and Plating	Brass, Gold		Beryllium Copper, Gold	
Contact Plating Specification	30 µin minimum			
Dielectric Type	PTFE		PTFE	
Body Material and Plating	Brass, Nickel		Brass, Nickel	
Body Plating Specification	100 µin minimum			
Coupling Nut Material and Plating			Brass, Nickel	
Hex Size			5/16 inch	
Torque	3 in-lbs [0.34 Nm]			


Mechanical Specification Notes:

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

Typical Performance Data



Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: N Female Bulkhead to Reverse Polarity SMA Male Right Angle Cable Using RG400 Coax PE3C5030

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com

^{*}All cable assemblies have a length tolerance of 1.5% or ± 3/8", whichever is greater.






RF Cable Assemblies Technical Data Sheet

PE3C5030

How to Order



Example: PE3C5030-12 = 12 inches long cable PE3C5030-100cm = 100 cm long cable

N Female Bulkhead to Reverse Polarity SMA Male Right Angle Cable Using RG400 Coax from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.


Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: N Female Bulkhead to Reverse Polarity SMA Male Right Angle Cable Using RG400 Coax PE3C5030

URL: https://www.pasternack.com/n-female-sma-male-rg400u-cable-assembly-pe3c5030-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451

PE3C5030 CAD DrawingN Female Bulkhead to Reverse Polarity SMA Male Right Angle Cable Using RG400 Coax



PE3C5030 REV 1.0

© 2018 Pasternack Enterprises All Rights Reserved