


PE3C6217

Plenum N Female to SMA Male Right Angle Low PIM Cable Using SPP-250-LLPL Coax Using Times Microwave Parts

RF Cable Assemblies Technical Data Sheet



Description

Pasternack's PE3C6217 type N female to SMA male right angle cable using SPP-250-LLPL coax is part of our full line of RF components available for same-day shipping. Pasternack's corrugated RF cable assemblies are ideal for applications where durability and high power are needed. This Pasternack type N to SMA cable assembly has a female to male gender configuration with 50 ohm corrugated SPP-250-LLPL coax. The PE3C6217 type N female to SMA male cable assembly operates to 5.8 GHz. Our low PIM design also offers excellent passive intermodulation performance with PIM levels better than -160 dBc. The right angle SMA interface on the SPP-250-LLPL cable allows for easier connections in tight spaces. Times Microwave cable is used in each assembly and TMS components are used to form connections with the super flexible low PIM cable. These cable assemblies are expertly built to satisfy your specific need with high quality Times Microwave Systems manufactured parts.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: Plenum N Female to SMA Male Right Angle Low PIM Cable Using SPP-250-LLPL Coax Using Times Microwave Parts PE3C6217

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451 Sales@Pasternack.com • Techsupport@Pasternack.com

Calos and asternaok.com - reensupportar asternack.com





RF Cable Assemblies Technical Data Sheet

PE3C6217

Electrical Specifications

| Description | Minimum | Typical | Maximum | Units |
|-------------------------------|---------|--------------|---------|-----------------|
| Frequency Range | DC | | 5.8 | GHz |
| VSWR | | | 1.4:1 | |
| Velocity of Propagation | | 76 | | % |
| RF Shielding | 100 | | | dB |
| Passive Intermodulation | | -165 | -160 | dBc |
| Capacitance | | 27 [88.58] | | pF/ft [pF/m] |
| Inductance | | 0.067 [0.22] | | uH/ft [uH/m] |
| DC Resistance Inner Conductor | | 3 [9.84] | | Ω/1000ft [Ω/Km] |

Specifications by Frequency

| Description | F1 | F2 | F3 | F4 | F5 | Units |
|-----------------------|-------|-------|-------|-------|-------|-------|
| Frequency | 0.45 | 0.7 | 1 | 2.5 | 5.8 | GHz |
| Insertion Loss (Max.) | 0.038 | 0.048 | 0.057 | 0.094 | 0.148 | dB/ft |
| | 0.12 | 0.16 | 0.19 | 0.31 | 0.49 | dB/m |

Electrical Specification Notes:

PIM test results vary between cables

Insertion Loss does not include the loss of the connectors. Insertion Loss is estimated as 0.1 dB for the female connector and 0.15*SQRT(FGHz) dB for the male connector.

Mechanical Specifications

Cable Assembly

| Description | Minimum | Typical | Maximum | Units |
|------------------------------|---------|-------------|---------|---------|
| Jacket Diameter | | 0.28 [7.11] | | in [mm] |
| One Time Minimum Bend Radius | 1.25 | | | in |
| Bending Moment | | 0.8 | | lbs-ft |

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: Plenum N Female to SMA Male Right Angle Low PIM Cable Using SPP-250-LLPL Coax Using Times Microwave Parts PE3C6217

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451 Sales@Pasternack.com • Techsupport@Pasternack.com





RF Cable Assemblies Technical Data Sheet

PE3C6217

Cable Characteristics

| Specification | |
|----------------------------------|--|
| SPP-250-LLPL | |
| 50 Ohms | |
| Solid | |
| Copper | |
| PTFE | |
| 1 | |
| Helically Corrugated Copper Tube | |
| Copper | |
| 0.25 in [6.35 mm] | |
| FEP, Blue | |
| | SPP-250-LLPL 50 Ohms Solid Copper PTFE 1 Helically Corrugated Copper Tube Copper 0.25 in [6.35 mm] |

Connector Characteristics

| Description | Connector 1 | Connector 2 |
|---------------------------------------|-------------------------|-------------------------|
| Туре | N Female | SMA Male Right Angle |
| Impedance | 50 Ohms | 50 Ohms |
| Contact Material and Plating | Phosphor Bronze, Silver | Phosphor Bronze, Silver |
| Contact Plating Specification | 196 µin | 196 µin |
| Dielectric Type | PTFE | PTFE |
| Outer Conductor Material and Plating | Brass, Tri-Metal | |
| Outer Conductor Plating Specification | 118 µin | |
| Body Material and Plating | Brass, Tri-Metal | Brass, Tri-Metal |
| Body Plating Specification | 118 µin | 118 µin |
| Coupling Nut Material and Plating | | Brass, Tri-Metal |
| Coupling Nut Plating Specification | | 118 µin |
| Torque | 10 in-lbs 1.13 Nm | 10 in-lbs 1.13 Nm |

Mechanical Specification Notes:

Environmental Specifications

| Description | Specification | |
|-----------------------------|-------------------|--|
| Temperature Operating Range | -55 to +200 deg C | |
| Temperature Storage Range | -55 to +200 deg C | |
| Plenum Rating | UL910 | |
| - | | |

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: Plenum N Female to SMA Male Right Angle Low PIM Cable Using SPP-250-LLPL Coax Using Times Microwave Parts PE3C6217

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451 Sales@Pasternack.com • Techsupport@Pasternack.com

© 2019 Pasternack Enterprises All Rights Reserved





RF Cable Assemblies Technical Data Sheet PE3C6217 Compliance Certifications (see product page for current document) **Plotted and Other Data** Notes: • Values at 25°C, sea level. **Typical Performance Data** PIM LEVEL Test Result> dBc **PIM LEVEL** <Test Result> dBc Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: Plenum N Female to SMA Male Right Angle Low PIM Cable Using SPP-250-LLPL Coax Using

Times Microwave Parts PE3C6217


Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451 Sales@Pasternack.com • Techsupport@Pasternack.com





RF Cable Assemblies Technical Data Sheet

PE3C6217



Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451 Sales@Pasternack.com • Techsupport@Pasternack.com PE3C6217 CAD Drawing Plenum N Female to SMA Male Right Angle Low PIM Cable Using

SPP-250-LLPL Coax Using Times Microwave Parts

