



# **RF Cable Assemblies Technical Data Sheet**

PE3TC1000

# Configuration

• Connector 1: 1.85mm Male

• Connector 2: 1.85mm Male Right Angle

Cable Type: PE-VNA-HF

#### **Features**

- Max Frequency 70 GHz
- Shielding Effectivity > 100 dB
- 78% Phase Velocity
- Triple Shielded
- Designed for use as VNA test port extenders
- Highly flexible armored cable construction
- 1.40:1 VSWR to 70 GHz
- · Excellent amplitude and phase stability with flexure
- Non-conductive protective Nomex outer sleeve
- · Each serialized assembly comes with test data
- · In-stock and ready to ship same-day

# **Applications**

- General Purpose
- Laboratory Use

- Vector Network analyzer test port extenders
- · Semiconductor probe testing
- · Precise bench-top testing
- Lab and production testing

# Description

Pasternack high performance high flex VNA test cables are designed to provide customers repeatable and accurate VNA measurements. These Test cables have excellent electrical properties including low Insertion Loss, low VSWR and phase stability of +/- 8° with flexure. The braided stainless steel armoring provides a rugged, but flexible cable with a life exceeding 100,000 flex cycles. The rugged connectors provide up to 5,000 mating cycles when attached with proper care. The flexibility of these cables makes it easier and safer to test your Device Under Test (DUT). When used with the appropriate calibration kit, these test cables effectively extend the test port of the VNA allowing for accurate measurements of devices that cannot be directly connected to a network analyzer test port.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: 1.85mm Male to 1.85mm Male Right Angle Precision Cable Using High Flex VNA Test Coax PE3TC1000

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451





# RF Cable Assemblies Technical Data Sheet

# PE3TC1000

# **Electrical Specifications**

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		70	GHz
VSWR		/ (35)	1.4:1	
Velocity of Propagation		78		%
RF Shielding	100			dB
Group Delay		1.34 [4.4]		ns/ft [ns/m]
Capacitance		25.9 [84.97]		pF/ft [pF/m]
Input Power (Average)			18	Watts
Phase Stability with Flexure		8		Degrees

### Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	5	10	20	40	67	GHz
Insertion Loss (Max.)	0.48	0.68	1	1.45	1.95	dB/ft
	1.57	2.23	3.28	4.76	6.4	dB/m
Power Handling (Max.)					18	W

Electrical Specification Notes: Values at 25°C, sea level.

## **Mechanical Specifications**

# Cable Assembly

### Cable

Cable Type
Impedance
Inner Conductor Type
Inner Conductor Material and Plating
Dielectric Type
Number of Shields

Shield Layer 1 Shield Layer 2 Shield Layer 3 Jacket Diameter

One Time Minimum Bend Radius Flat Plate Crush

PE-VNA-HF 50 Ohms Solid Copper, Silver

Copper, Silver PTFE

3

Silver Plated Copper Tape Silver Plated Copper Braid Silver Plated Copper Braid

0.27 in [6.86 mm]

1 in [25.4 mm]

317 lbs/in [5.66 Kg/mm]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: 1.85mm Male to 1.85mm Male Right Angle Precision Cable Using High Flex VNA Test Coax PE3TC1000

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com





# **RF Cable Assemblies Technical Data Sheet**

# **PE3TC1000**

#### **Connectors**

Description	Connector 1	Connector 2 1.85mm Male Right Angle	
Туре	1.85mm Male		
Impedance	50 Ohms	50 Ohms	
Contact Material and Plating	Beryllium Copper, Gold	Beryllium Copper, Gold	
Dielectric Type	ULTEM	ULTEM	
Outer Conductor Material and Plating		Passivated Stainless Steel	
Body Material and Plating	Passivated Stainless Steel	Passivated Stainless Steel	
Coupling Nut Material and Plating	Passivated Stainless Steel		
Torque	8 in-lbs [0.9 Nm]	8 in-lbs [0.9 Nm]	

Mechanical Specification Notes:

### **Environmental Specifications**

Temperature

**Operating Range** 

-65 to +125 deg C

Compliance Certifications (see product page for current document)

#### **Plotted and Other Data**

Notes:

Values at 25°C, sea level.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: 1.85mm Male to 1.85mm Male Right Angle Precision Cable Using High Flex VNA Test Coax PE3TC1000

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451


<sup>\*</sup>All cable assemblies have a length tolerance of 1.5% or ± 3/8", whichever is greater.





# **RF Cable Assemblies Technical Data Sheet**

**PE3TC1000** 



Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: 1.85mm Male to 1.85mm Male Right Angle Precision Cable Using High Flex VNA Test Coax PE3TC1000






# **RF Cable Assemblies Technical Data Sheet**

# PE3TC1000

#### **How to Order**



Example: PE3TC1000-12 = 12 inches long cable PE3TC1000-100cm = 100 cm long cable

1.85mm Male to 1.85mm Male Right Angle Precision Cable Using High Flex VNA Test Coax from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: 1.85mm Male to 1.85mm Male Right Angle Precision Cable Using High Flex VNA Test Coax PE3TC1000

URL: https://www.pasternack.com/1.85mm-male-1.85mm-male-vna-cable-cable-assembly-pe3tc1000-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451

**PE3TC1000 CAD Drawing**1.85mm Male to 1.85mm Male Right Angle Precision Cable Using High Flex VNA Test Coax

