



Electromechanical Relay Switches Technical Data SheetPE7

PE71S6201

 Features Single Pole Double Throw Re DC to 10 GHz Frequency Rar 1M Cycle Min Operating Life 	• Isolation	 Insertion Loss 0.6 dB max Isolation 60 dB min 50 Watts Avg Power Max 			
 Failsafe Actuator TTL Logic Driver, Position Ind Diodes 	Switching	g Sequence Break Before Make			
Applications					
Test & Measurement	 Communications System 	Instrumentation			

Description

The PE71S6201 is a Single Pole Double Throw Electromechanical Relay Switch that operates from DC to 10 GHz and has a rating of 50 Watts input power (CW) in a Break Before Make condition. The design features a Failsafe Actuator with TTL Logic Driver, Position Indicators, Suppression Diodes and is rated for 1M Life Cycles for high reliability operation. Insertion loss is specified from 0.2 dB max and Isolation from 80 dB min, with +28 Vdc operating voltage and performance is guaranteed over -25°C to +65°C. The package interface uses solder terminals and TNC Female connectors.

Electrical Specifications

Switch Type Actuator Type Switching Sequence Actuator Options TTL Control SPDT, Reflective Failsafe Break Before Make Indicators, TTL Logic, Diodes on: 2.4 to 5 Volts off: 0 to 0.8 Volts

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		10	GHz
Impedance		50		Ohms
Operating Voltage		28		Volts
Actuating Current @ 28 Volts		125		mA
VSWR			1.6:1	
Insertion Loss			0.6	dB
Isolation	60			dB
Input Power (CW)			50	Watts
(at 10 GHz)				

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: SPDT Electromechanical Relay Failsafe Switch DC to 10 GHz, TNC, 50 Watts, 28V Control, Indicators, TTL, Diodes PE71S6201

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 Phone: (866) 727-8376 or (949) 261-1920 • Fax: (949) 261-7451





Electromechanical Relay Switches Technical Data

PE71S6201

Description	F1	F2	F3	F4	F5	Units		
Frequency Range	DC to 4	4 to 10				GHz		
VSWR, Max	1.2:1	1.6:1						
Insertion Loss, Max	0.2	0.6				dB		
Isolation, Min	80	60				dB		
hanical Specification	ıs							
Length Width/Diameter Height			1.7	96 in [49.78 n 76 in [44.7 mr 72 in [18.29 n	n]			
Weight Body Material and Platin Package Type			0.344 lbs [156.04 g] Aluminum Connectorized Module					
Operating Life Switching Time				1,000,000 Cycles 50 ms Max				
Connectors RF Connector Type RF Connector Contact Material and Plating RF Connector Body Material and Plating Control Connector		Be Pa	TNC Female Beryllium Copper, Gold Passivated Stainless Steel Solder Pin					
Vironmental Specifications Temperature Operating Range ESD Sensitivity		ES	-25 to +65 deg C ESD Sensitive Material. Transport material in Appr ESD bags. Handle in approved ESD Workstation.					
Environmental Specifica Designed to meet MIL-D								
npliance Certificatior Not RoHS Compliant	15 (visit www.I	Pasternack.com	m for current	document)				

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: SPDT Electromechanical Relay Failsafe Switch DC to 10 GHz, TNC, 50 Watts, 28V Control, Indicators, TTL, Diodes PE71S6201


Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 Phone: (866) 727-8376 or (949) 261-1920 • Fax: (949) 261-7451





Electromechanical Relay Switches Technical Data

PE71S6201



Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: SPDT Electromechanical Relay Failsafe Switch DC to 10 GHz, TNC, 50 Watts, 28V Control, Indicators, TTL, Diodes PE71S6201


Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 Phone: (866) 727-8376 or (949) 261-1920 • Fax: (949) 261-7451





Electromechanical Relay Switches Technical Data

PE71S6201



SPDT Electromechanical Relay Failsafe Switch DC to 10 GHz, TNC, 50 Watts, 28V Control, Indicators, TTL, Diodes from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: SPDT Electromechanical Relay Failsafe Switch DC to 10 GHz, TNC, 50 Watts, 28V Control, Indicators, TTL, Diodes PE71S6201


URL: http://www.pasternack.com/tnc-sp6t-electromechanical-relay-switch-10-ghz-indicators-failsafe-ttl-logic-pe71s6201-p. aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 Phone: (866) 727-8376 or (949) 261-1920 • Fax: (949) 261-7451

PE71S6201 CAD Drawing

SPDT Electromechanical Relay Failsafe Switch DC to 10 GHz, TNC, 50 Watts, 28V Control, Indicators, TTL, Diodes



5

PE71S6201 CAD Drawing

SPDT Electromechanical Relay Failsafe Switch DC to 10 GHz, TNC, 50 Watts, 28V Control, Indicators, TTL, Diodes

