

## MMCX Plug Connector Crimp/Solder Attachment for RG178, RG196



## **RF Connectors Technical Data Sheet**

PE4897

## Configuration

- MMCX Plug Connector
- BS EN 122340
- 50 Ohms

#### **Features**

- Max. Operating Frequency 3 GHz
- Excellent VSWR of 1.22:1

- Straight Body Geometry
- RG178, RG196 Interface Type
- Crimp/Solder Attachment
- Gold Plated Brass Contact
- 30 µin minimum contact plating

## **Applications**

General Purpose Test

Custom Cable Assemblies

#### **Description**

Pasternack's PE4897 MMCX plug connector with crimp/solder attachment for RG178 and RG196 is part of our full line of RF components available for same-day shipping. Our MMCX plug connector operates up to a maximum frequency of 3 GHz and offers excellent VSWR of 1.22:1.

Our MMCX plug connector PE4897 datasheet specifications and drawing with dimensions are shown below in this PDF. Pasternack's broad catalog of RF, microwave and millimeter wave connectors allows designers to configure and customize their signal connections however they like. Whether the need is to provide an I/O for a board design, or simply create a custom cable assembly configuration, Pasternack has the right connector for the job. Pasternack can also expertly build your custom cable assemblies for you and ship same-day.

#### **Electrical Specifications**

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		3	GHz
VSWR			1.22:1	
Operating Voltage (AC)			170	Vrms
Dielectric Withstanding Voltage (AC)			500	Vrms

## **Mechanical Specifications**

Size

 Length
 0.453 in [11.51 mm]

 Width/Dia.
 0.138 in [3.51 mm]

 Weight
 0.003 lbs [1.36 g]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: MMCX Plug Connector Crimp/Solder Attachment for RG178, RG196 PE4897

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com



# MMCX Plug Connector Crimp/Solder Attachment for RG178, RG196



## **RF Connectors Technical Data Sheet**

**PE4897** 

#### Material Specifications

Description	Material	Plating
Contact	Brass	Gold 30 µin minimum
Insulation	PTFE	
Body	Brass	Gold 3 μin minimum

### **Environmental Specifications**

**Temperature** 

**Operating Range** 

-55 to +155 deg C

Compliance Certifications (see product page for current document)

#### **Plotted and Other Data**

Notes:

MMCX Plug Connector Crimp/Solder Attachment for RG178, RG196 from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: MMCX Plug Connector Crimp/Solder Attachment for RG178, RG196 PE4897

URL: https://www.pasternack.com/mmcx-plug-standard-rg178-rg196-connector-pe4897-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451

