


SPECIFICATIONS

Frequency Range	902-928 MHz
Impedance	50 Ohm
VSWR	≤1.8
Gain	9 dBi
Polarization	Vertical Linear
Radiation Pattern	Directional
Pole Diameter	.9-1.8 in.
Connector	N Female
Weight	855.5 g (est)
Temperature Range	-40°C to +85°C

Pole Mount Installation




U Bolt **Bracket**

1. PLACE THE U BOLTS AND BRACKETS ON POLE AS SHOWN.

2. PLACE THE ANTENNA ON THE U BOLTS AND SECURE USING PROVIDED NUTS.

3. ATTACH TO CABLE ASSEMBLY.

Included Hardware For Wall Mount



PASTERNAK ENTERPRISES, INC.

P.O BOX 16759, IRVINE, CA 92623
PHONE (949) 261-1920 FAX (949) 261-7451

WEB ADDRESS: www.pasternack.com
E-MAIL ADDRESS: sales@pasternack.com

COAXIAL & FIBER OPTICS

DWG TITLE

PE51023

DES. 902-928 MHz DIRECTIONAL PANEL OUTDOOR ANTENNA, 9 dBi, VERTICAL POLARIZATION

REV. A	FSCM NO. 53919	CAD FILE 021508	SCALE N/A	SIZE A	127
--------	----------------	-----------------	-----------	--------	-----

NOTES:

1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.
2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.
3. DIMENSIONS ARE IN INCHES.