



## 2.4/5.8 GHz 5/6 dBi Dual Band Omni Antenna

### Antennas Technical Data Sheet

**PE510M1002**

#### Features

- High Performance in a compact lightweight design
- Durable UV-Stable fiberglass radome with vented end cap and drain holes in base
- All weather operation
- Integral N-Female connector
- Includes mast mounting kit

#### Applications

- 2.4/4.9/5.1/5.3/5.4/5.8 GHz Wireless LAN systems
- IEEE 802.11a/b/g/n and 802.11ac compatible
- Homeland Security and Public Safety band
- WiMAX and WiFi applications
- Multipoint and mobile applications

#### Description

The HyperLink brand PE510M1002 is an economical yet high performance dual band omnidirectional antenna designed for operation in the 2.4 GHz and 4.9/5.8 GHz frequency bands. Compact and lightweight, these antennas are ideally suited multipoint applications where wide coverage is desired.

The PE510M1002 antennas feature an integral N-Female bulkhead type connector that can mount through the wall of an equipment enclosure. Also included is a mast mounting kit which consists of a heavy-duty steel bracket and a pair of U-bolts. This kit allows for installations on masts up to 2.0" in diameter. A vented end cap and drain holes in the base help prevent moisture build-up inside the antenna. These features allow the antenna to be mounted in up or down positions.

#### Configuration

Design	Omni
Band Type	Dual
Radiation Pattern	Omni Directional
Polarization	Vertical
Connector Type	N Female
Number of Ports	1
Lightning Protection	DC Short

#### Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	2,400		5,850	MHz
Input VSWR			2.5:1	
Impedance		50		Ohms
Input Power			50	Watts

#### Specifications by Band

Description	Band 1	Band 2	Band 3	Band 4	Band 5	Units
Range	2.4 to 2.5	4.9 to 5.85				GHz
Gain	5	6				dBi
Horizontal Beam Width	360					Degrees
Vertical Beam Width	45					Degrees
Maximum Input Power	50	50				Watts

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [2.4/5.8 GHz 5/6 dBi Dual Band Omni Antenna PE510M1002](#)



## 2.4/5.8 GHz 5/6 dBi Dual Band Omni Antenna

### Antennas Technical Data Sheet

**PE51OM1002**

#### Mechanical Specifications

Radome Material	Fiberglass
<b>Size</b>	
Overall Length	11.6 in [294.64 mm]
Width	0.75 in [19.05 mm]
Height	0.75 in [19.05 mm]
Mounting Mast Diameter	2 in [50.80 mm]
Weight	1.3 lbs [589.67 g]

#### Environmental Specifications

<b>Temperature</b>	
Operating Range	-40 to +85 deg C

**Compliance Certifications** (see [product page](#) for current document)

#### Plotted and Other Data

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [2.4/5.8 GHz 5/6 dBi Dual Band Omni Antenna PE51OM1002](#)




## 2.4/5.8 GHz 5/6 dBi Dual Band Omni Antenna

### Antennas Technical Data Sheet

**PE510M1002**

#### RF Antenna Patterns – PE510M1002



2.4/5.8 GHz 5/6 dBi Dual Band Omni Antenna from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in “SEARCH” on website) to obtain additional part information including price, inventory and certifications: [2.4/5.8 GHz 5/6 dBi Dual Band Omni Antenna PE510M1002](https://www.pasternack.com/dual-antenna-0-dbi-gain-n-pe510m1002-p.aspx)


URL: <https://www.pasternack.com/dual-antenna-0-dbi-gain-n-pe510m1002-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

# PE51OM1002 CAD Drawing

## 2.4/5.8 GHz 5/6 dBi Dual Band Omni Antenna

REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
	INITIAL RELEASE	2/13/2020	M.MILLER



**UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES DIMENSIONS IN [ ] ARE MILLIMETERS**

**TOLERANCES:**

.X = ±.2 [5.08]	FRACTIONS ± 1/32
.XX = ±.02 [ .51]	ANGLES ± 1°
.XXX = ±.005 [ .13]	

**CABLE LENGTH (L) TOLERANCES:**

L ≤ 12 [305]	± .1 [25] / -0
12 [305] < L ≤ 60 [1524]	± .2 [51] / -0
60 [1524] < L ≤ 120 [3048]	± .4 [102] / -0
120 [3048] < L ≤ 300 [7620]	± .6 [152] / -0
300 [7620] < L = +5% / L / -0	

ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY.

**THIRD-ANGLE PROJECTION**

THE INFORMATION AND DESIGN IN THIS DOCUMENT IS THE PROPERTY OF PASTERNAK CORPORATION. ALL RIGHTS RESERVED.

SHEET 1 OF 1

SCALE N/A

**Pasternack Enterprises, Inc.**  
 P. O. Box 16759, Irvine, CA 92623.  
 Phone: 1.949.261.1920 | 1.866.727.8376  
 Fax: 1.949.261.7451  
 Website: www.pasternack.com  
 E-mail: sales@pasternack.com

SIZE	CAGE CODE	DRAWN BY	ITEM NO.	REV
A	53919	K.DANG	PE51OM1002	A

**REGULATORY COMPLIANCE:**  
 EU ROHS DIRECTIVE (MOST RECENT RELEASED VERSION)

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.