



# Flexible RG223 Coax Cable Double Shielded with Black PVC Jacket

### **TECHNICAL DATA SHEET**

**RG223/U** 

Configuration

Inner Conductor Material and Plating Copper, Silver

Dielectric Type PE

Shield Materials Silver Plated Copper Braid, Silver Plated Copper Braid

Jacket Material and Color PVC, Black

**Electrical Specifications** 

Impedance, Ohms 50
Velocity of Propagation, % 66
Maximum Operating Fragues as CUE

Maximum Operating Frequency, GHz
Capacitance, pF/ft [pF/m]
12.4
30.8 [101.05]

Maximum Operating Voltage, Volts 1,900

**Electrical Specifications by Frequency** 

Frequency 1

Frequency, MHz 100 Attenuation, dB/100ft [dB/100m] 4 [13.12]

Frequency 2

Frequency, MHz 400 Attenuation, dB/100ft [dB/100m] 8.2 [26.9]

Frequency 3

Frequency, MHz 1000

Attenuation, dB/100ft [dB/100m] 13.4 [43.96]

Frequency 4

Frequency, GHz

Attenuation, dB/100ft [dB/100m] 24.8 [81.36]

Frequency 5

Frequency, GHz

Attenuation, dB/100ft [dB/100m] 33.5 [109.91]

Frequency 6

Frequency, GHz 1

Attenuation, dB/100ft [dB/100m] 54.1 [177.49]

**Mechanical Specifications** 

Temperature

Operating Range, deg C -20 to +80

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: Flexible RG223 Coax Cable Double Shielded with Black PVC Jacket RG223/U





## Flexible RG223 Coax Cable Double Shielded with Black PVC Jacket

### **TECHNICAL DATA SHEET**

**RG223/U** 

**Inner Conductor** 

Number of Strands

Material Copper
Plating Silver
Diameter, in [mm] 0.035 [0.89]

Dielectric:

Type PE

Diameter, in [mm] 0.116 [2.95]

Shield:

Number of

Material 1 Silver Plated Copper Braid
Material 2 Silver Plated Copper Braid

Diameter, in [mm] 0.156 [3.96]

Jacket:

 Material
 PVC

 Diameter, in [mm]
 0.21 [5.33]

 Color
 Black

 One Time Minimum Bend Radius, in [mm]
 0.21 [5.33]

 Repeated Minimum Bend Radius, in [mm]
 1 [25.4]

 Weight, lbs/ft [Kg/m]
 0.038 [0.06]

Compliance Certifications (visit www.Pasternack.com for current document)

**RoHS Compliant** 

REACH Compliant 06/18/2012

#### **Plotted and Other Data**

Notes:

Values at +25 °C, sea level

Flexible RG223 Coax Cable Double Shielded with Black PVC Jacket from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: Flexible RG223 Coax Cable Double Shielded with Black PVC Jacket RG223/U

URL: http://www.pasternack.com/flexible-0.216-rg223-50-ohm-coax-cable-pvc-jacket-rg223-u-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com

RG223/U CAD Drawing
Flexible RG223 Coax Cable Double Shielded with Black PVC Jacket

