



### **PIN Diode Switches Technical Data Sheet**

PE71S2017

#### **Features**

- · SPDT Reflective Switch
- 2 GHz to 26.5 GHz
- · Insertion Loss 3 dB max

- Isolation 30 dB min
- Power Input +30 dBm CW max

### **Applications**

- Test & Measurement
- Military Communication
- Commercial Communication

#### Description

The PE71S2017 is a SINGLE POLE DOUBLE THROW (SPDT) REFLECTIVE PIN DIODE SWITCH that operates from 2 to 26.5 GHz. Electrical performance includes 3 dB max insertion loss, -7 dB max return loss, 30 dB min isolation, and 100 nsec max switching speed. The design incorporates TTL-compatible driver circuitry for accurate logic control. Operational temperature range is -30°C to +60°C and dual voltage controls of +5 Vdc and -5 Vdc are required. The package interface uses solder terminals and SMA Female connectors.

### **Electrical Specifications**

Description	Minimum	Typical	Maximum	Units
Frequency Range	2		26.5	GHz
Impedance		50		Ohms
Return Loss			-7	dB
Insertion Loss			3	dB
solation	30			dB
Switching Time			100	ns
Input Power (CW)			1	Watts
Positive Operating Voltage		5		Vdc
Negative Operating Voltage		-5		Vdc
Operating Temperature	-30		+60	deg C

**Electrical Specification Notes:** 

Specified switching time includes TTL driver delay.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: SPDT PIN Diode Switch Operating From 2 GHz to 26.5 GHz Up to +30 dBm and SMA PE71S2017

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com





### **PIN Diode Switches Technical Data Sheet**

PE71S2017

#### **Mechanical Specifications**

Size

Length Width

Height

Weight Design

RF Connector

TTL Control Connector

1 in [25.4 mm] 1.2 in [30.48 mm] 0.6 in [15.24 mm]

11 lbs [4.99 Kg] Reflective, SPDT SMA Female SMA Female

#### **Environmental Specifications**

**Temperature** 

Operating Range ESD Sensitivity

-30 to +60 deg C

ESD Sensitive Material. Transport material in Approved ESD bags. Handle only in ESD Workstation.

Compliance Certifications (see product page for current document)

**Plotted and Other Data** 

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: SPDT PIN Diode Switch Operating From 2 GHz to 26.5 GHz Up to +30 dBm and SMA PE71S2017







# **PIN Diode Switches Technical Data Sheet**

#### PE71S2017

#### **Typical Performance Data**





Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: SPDT PIN Diode Switch Operating From 2 GHz to 26.5 GHz Up to +30 dBm and SMA PE71S2017


Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451





## **PIN Diode Switches Technical Data Sheet**

#### PE71S2017



SPDT PIN Diode Switch Operating From 2 GHz to 26.5 GHz Up to +30 dBm and SMA from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: SPDT PIN Diode Switch Operating From 2 GHz to 26.5 GHz Up to +30 dBm and SMA PE71S2017

URL: https://www.pasternack.com/spdt-pin-diode-switch-26.5-ghz-30-dbm-sma-pe71s2017-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

# PE71S2017 CAD Drawing

SPDT PIN Diode Switch Operating From 2 GHz to 26.5 GHz Up to +30 dBm and SMA

