

SPDT Electromechanical Relay Failsafe Switch DC to 12.4 GHz, N, 50 Watts, 28V Control



Electromechanical Relay Switches Technical Data Sheet

PE71S6151

Features

- Single Pole Double Throw Relay Switch
- DC to 12.4 GHz Frequency Range
- 1M Cycle Min Operating Life
- Failsafe Actuator

- · Insertion Loss 0.6 dB max
- Isolation 60 dB min
- 50 Watts Avg Power Max
- · Switching Sequence Break Before Make

Applications

- · Test & Measurement
- · Communications System
- Instrumentation

Description

The PE71S6151 is a Single Pole Double Throw Electromechanical Relay Switch that operates from DC to 12.4 GHz and has a rating of 50 Watts input power (CW) in a Break Before Make condition. The design features a Failsafe Actuator and is rated for 1M Life Cycles for high reliability operation. Insertion loss is specified from 0.2 dB max and Isolation from 80 dB min, with +28 Vdc operating voltage and performance is guaranteed over -55°C to +85°C. The package interface uses solder terminals and N Female connectors.

Electrical Specifications

Switch Type Actuator Type Switching Sequence SPDT, Reflective Failsafe Break Before Make

Description Minimum Maximum Units Typical Frequency Range DC 12.4 GHz Impedance Ohms Operating Voltage 28 Volts Actuating Current @ 28 Volts 130 mΑ **VSWR** 1.6:1 Insertion Loss 0.6 dB Isolation 60 dB Input Power (CW) 50 Watts

(at 12.4 GHz)

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: SPDT Electromechanical Relay Failsafe Switch DC to 12.4 GHz, N, 50 Watts, 28V Control PE71S6151

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com



SPDT Electromechanical Relay Failsafe Switch DC to 12.4 GHz, N, 50 Watts, 28V Control



Electromechanical Relay Switches Technical Data

PE71S6151

Performance by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency Range	DC to 2	2 to 4	4 to 12.4			GHz
VSWR, Max	1.15:1	1.2:1	1.6:1			
Insertion Loss, Max	0.2	0.25	0.6			dB
Isolation, Min	80	80	60			dB

Mechanical Specifications

Size

Length

Width/Diameter

Height

Weight

Body Material and Plating

Package Type

Operating Life

Switching Time

Connectors

RF Connector Type

RF Connector Contact Material and Plating

RF Connector Body Material and Plating

Control Connector

Environmental Specifications

-55 to +85 deg C

1.61 in [40.89 mm]

2.46 in [62.48 mm] 0.9 in [22.86 mm]

0.53 lbs [240.4 g]

Connectorized Module 1,000,000 Cycles

Beryllium Copper, Gold

Passivated Stainless Steel

Aluminum

50 ms Max

N Female

Solder Pin

ESD Sensitive Material. Transport material in Approved

ESD bags. Handle in approved ESD Workstation.

Temperature

Operating Range

ESD Sensitivity

Environmental Specification Notes:

Designed to meet MIL-DTL-3928

Compliance Certifications (visit www.Pasternack.com for current document)

Not RoHS Compliant

Plotted and Other Data

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: SPDT Electromechanical Relay Failsafe Switch DC to 12.4 GHz, N, 50 Watts, 28V Control PE71S6151

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 Phone: (866) 727-8376 or (949) 261-1920 • Fax: (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com



SPDT Electromechanical Relay Failsafe Switch DC to 12.4 GHz, N, 50 Watts, 28V Control




Electromechanical Relay Switches Technical Data

PE71S6151

Typical Performance Data





Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: SPDT Electromechanical Relay Failsafe Switch DC to 12.4 GHz, N, 50 Watts, 28V Control PE71S6151

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com




SPDT Electromechanical Relay Failsafe Switch DC to 12.4 GHz, N, 50 Watts, 28V Control



Electromechanical Relay Switches Technical Data

PE71S6151



SPDT Electromechanical Relay Failsafe Switch DC to 12.4 GHz, N, 50 Watts, 28V Control from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: SPDT Electromechanical Relay Failsafe Switch DC to 12.4 GHz, N, 50 Watts, 28V Control PE71S6151


URL: http://www.pasternack.com/n-spdt-electromechanical-relay-switch-12.4-ghz-failsafe-pe71s6151-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451

PE71S6151 CAD Drawing

SPDT Electromechanical Relay Failsafe Switch DC to 12.4 GHz, N, 50 Watts, 28V Control



PE71S6151 CAD Drawing
SPDT Electromechanical Relay Failsafe Switch DC to 12.4 GHz, N, 50 Watts, 28V Control

