


NOTICE OF PROPRIETARY RIGHTS THIS DOCUMENT CONTAINS CONFIDENTIAL TECHNICAL DATA, INCLUDING TRADE SECRETS, PROPRIETARY TO TIMES MICROWAVE SYSTEMS. DISCLOSURE OF THIS DATA IS EXPRESSLY CONDITIONED UPON YOUR ASSENT THAT ITS USE IS LIMITED TO USE WITHIN YOUR COMPANY ONLY. ANY OTHER USE IS STRICTLY PROHIBITED WITHOUT THE PRIOR WRITTEN CONSENT OF TIMES MICROWAVE SYSTEMS.

SYM	REVISION DESCRIPTION	DFTM	DATE	APPD	DATE
A	RELEASED FOR PRODUCTION	K.A.M.	1/25/11	J.D.B.	2/2/11
B	CHANGED PER CDC #34511	D.J.H.	11/30/11	J.D.B.	12/1/11



Reference standard IEC60169-4

I. Electric Performance

Nominal Impedance(Ω): 50
Frequency Range: DC-6GHz
VSWR: ≤ 1.10 (DC-3G)
 ≤ 1.20 (3G-6G)
PIM(dBc) ≤ -160
INSERT LOSS: ≤ 0.05
Insulation resistance(M Ω) > 10000
Proof voltage(V) 4000
Conductor resistance(m Ω) outer conductor < 0.2
inner conductor < 0.8

II. Mechanical Performance

Nut torque 25N.m
(Nut)Whorl pull 1000N
Tensile force(cable-connect) 500N
Torsion(cable-connect) 5N.m

III. Material and plating :

Inner conductor Spring Copper
Outer conductor Brass
Nut Brass
Gasket Silicone rubber
Insulator TPX
Plating Ag 5um
Plating Copper-tin-zinc 2um
Plating Ni 5um

IV. Environment

Temp.range $-40^{\circ}\text{C} \sim +85^{\circ}\text{C}$
Weather standard IEC 60068 40 / 085/ 21
Thermal shock US MIL-STD 202,Meth.107,Cond.B
Vibration US MIL-STD 202,Meth.204,Cond.B
Shock US MIL-STD 202,Meth.213,Cond.I
Waterproofing standard IP68

V. Assembly: inner and outer conductor installed

VI. ROHS Compliant.

MATL:		UNLESS OTHERWISE SPECIFIED			DFTM. K. A. M.	TIMES MICROWAVE SYSTEMS		
		ALL DIMENSIONS ARE IN mm			DATE 1/25/11			
USED ON: 0					CHKD. J. D. B.	EZ-SW540-716MC CONNECTOR, 7/16 MALE FOR LMR-SW540 CABLE		
					DATE 2/2/11			
					APPD. J. D. B.			
SCALE: ~	DWG. SIZE A	DO NOT SCALE DRAWING	CODE IDENT	68999	DATE 2/2/11	SHEET 1 of 1	SD3190-2622	REV B