



3 dB Fixed Attenuator, 7/16 DIN Female To N Female
Directional Rated To 50 Watts Up To 7.5 GHz

TECHNICAL DATA SHEET

PE7316-3

3 dB Fixed Attenuator, 7/16 DIN Female To N Female Directional Rated To 50 Watts Up To 7.5 GHz

Configuration

| | |
|---------------------------|-----------------------------------|
| Design | Fixed, Directional Attenuator |
| Connector 1 | 7/16 DIN Female |
| Connector 2 | N Female |
| Body Material and Plating | Aluminum Heatsink, Black Anodized |

Electrical Specifications

| | |
|----------------------------|-----------|
| Frequency Range, GHz | DC to 7.5 |
| Impedance, Ohms | 50 |
| Attenuation Value, dB | 3 |
| Maximum Input Power, Watts | 50 |
| Maximum VSWR | 1.45:1 |

Frequency 1

| | |
|--------------------------|---------|
| Range, GHz | DC to 6 |
| VSWR | 1.3:1 |
| Attenuation Accuracy, dB | 0.75 |

Frequency 2

| | |
|--------------------------|----------|
| Range, GHz | 6 to 7.5 |
| VSWR | 1.45:1 |
| Attenuation Accuracy, dB | 0.75 |

Mechanical Specifications

Temperature

| | |
|------------------------|-------------|
| Operating Range, deg C | -55 to +125 |
|------------------------|-------------|

Size

| | |
|-----------------|----------------|
| Length, in [mm] | 4.01 [101.85] |
| Width, in [mm] | 3 [76.2] |
| Height, in [mm] | 3 [76.2] |
| Weight, lbs [g] | 1.796 [814.65] |

Connector 1

| | |
|------------------------------|-----------------|
| Type | 7/16 DIN Female |
| Contact Material and Plating | Brass, Silver |
| Hex Size, In. | 11/16 |
| Body Material and Plating | Brass, Silver |

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [3 dB Fixed Attenuator, 7/16 DIN Female To N Female Directional Rated To 50 Watts Up To 7.5 GHz PE7316-3](#)

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal.



3 dB Fixed Attenuator, 7/16 DIN Female To N Female
Directional Rated To 50 Watts Up To 7.5 GHz

TECHNICAL DATA SHEET

PE7316-3

Connector 2

| | |
|--------------------------------------|-----------------------------|
| Type | N Female |
| Contact Material and Plating | Brass, Gold |
| Outer Conductor Material and Plating | Brass, Silver |
| Hex Size, In. | 11/16 |
| Body Material and Plating | Stainless Steel, Passivated |

Compliance Certifications (visit www.Pasternack.com for current document)

| | |
|----------------|-----|
| RoHS Compliant | Yes |
|----------------|-----|

Plotted and Other Data

| | |
|--------|---|
| Notes: | Values at 25 °C, sea level OUTPUT PORT HANDLES 5 WATTS MAX POWER |
| URL: | http://www.pasternack.com/3db-fixed-7-16-female-n-female-50-watts-attenuator-pe7316-3-p.aspx |


3 dB Fixed Attenuator, 7/16 DIN Female To N Female Directional Rated To 50 Watts Up To 7.5 GHz from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and fiber optic products maintain a 99% availability and are part of the broadest selection in the industry.

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal.

PE7316-3 CAD Drawing

3 dB Fixed Attenuator, 7/16 DIN Female To N Female
Directional Rated To 50 Watts Up To 7.5 GHz

| Table of Information | | Part Number Configuration | |
|----------------------|----------------|---------------------------|------------------|
| Connector Type | DIM "A" (REF.) | Input Connector | Output Connector |
| SMA Male | 0.68 | 7/16 Female | 7/16 Male |
| SMA Female | 0.54 | N Female | 7/16 Male |
| TNC Male | 0.98 | 7/16 Female | 7/16 Female |
| TNC Female | 0.94 | N Male | 7/16 Female |
| N Female | 0.95 | N Female | N Male |
| N Male | 0.98 | 7/16 Female | N Male |
| 7/16 Male | 1.12 | SMA Female | N Male |
| 7/16 Female | 1.16 | TNC Female | N Female |



NOTES:
1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.
2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.
3. DIMENSIONS ARE IN INCHES [mm].

DWG TITLE
PE73xx-yy

PE PASTERNAK®
Pasternack Enterprises, Inc.
P.O. Box 16759 | Irvine | CA | 92623
Phone: (949) 261-1920 | Fax: (949) 261-7451
Website: www.pasternack.com | E-Mail: sales@pasternack.com

FSCM NO. 53919

CAD FILE 102512

SCALE N/A

SIZE A

2233