


NOTICE OF PROPRIETARY RIGHTS THIS DOCUMENT CONTAINS CONFIDENTIAL TECHNICAL DATA, INCLUDING TRADE SECRETS, PROPRIETARY TO TIMES MICROWAVE SYSTEMS. DISCLOSURE OF THIS DATA IS EXPRESSLY CONDITIONED UPON YOUR ASSENT THAT ITS USE IS LIMITED TO USE WITHIN YOUR COMPANY ONLY. ANY OTHER USE IS STRICTLY PROHIBITED WITHOUT THE PRIOR WRITTEN CONSENT OF TIMES MICROWAVE SYSTEMS.

SYM	REVISION DESCRIPTION	DFTM	DATE	APPD	DATE
A	RELEASED FOR PRODUCTION	K.A.M.	1/24/11	J.D.B.	2/2/11
B	CHANGED PER CDC #34511	D.J.H.	11/30/11	J.D.B.	12/1/11



Reference standard IEC60169-4

I. Electric Performance

Impedance(Ω): 50
Frequency Range: 0-6GHz
VSWR: ≤ 1.2
PIM(dBc) ≤ -160
INSERT LOSS:(dB) ≤ 0.1
Insulation resistance(M Ω) > 5000
Work voltage(V) 2500
Conductor resistance(m Ω) outer conductor < 0.4
inner conductor < 0.8

II. Mechanical Performance

Inner conductor torque 3N.m
Mechanical wear 300

III. Material and plating :

Component	Material	Plating
Inner conductor	Spring Copper	Au 1.27um
Outer conductor	Brass	Copper-tin-zinc $> 2\mu\text{m}$
Insulator	PTFE	

IV. Environment

Temp.range	-55 $^{\circ}\text{C}$ ~+155 $^{\circ}\text{C}$
Weather standard	IEC 60068 55 / 155/ 56
Thermal shock	US MIL-STD 202,Meth.107,Cond.B
Vibration	US MIL-STD 202,Meth.204,Cond.B
Shock	US MIL-STD 202,Meth.213,Cond.I

V. Assembly: inner and outer conductor installed

VI. ROHS Compliant.

MATL:	UNLESS OTHERWISE SPECIFIED		DFTM. K. A. M.	TIMES MICROWAVE SYSTEMS		
	ALL DIMENSIONS ARE IN mm		DATE 1/24/11			
			CHKD. J. D. B.			
			DATE 2/2/11			
USED ON: 0			APPD. J. D. B.	EZ-SW540-NMC CONNECTOR, N MALE FOR LMR-SW540 CABLE		
SCALE: ~	DWG. SIZE A	DO NOT SCALE DRAWING	CODE IDENT 68999	DATE 2/2/11	SHT 1 of 1	SD3190-2620 REV B