



3 dB Fixed Attenuator, TNC Female To N Female  
Directional Rated To 50 Watts Up To 18 GHz

TECHNICAL DATA SHEET

PE7327-3

**3 dB Fixed Attenuator, TNC Female To N Female Directional Rated To 50 Watts Up To 18 GHz**

**Configuration**

|                           |                                   |
|---------------------------|-----------------------------------|
| Design                    | Fixed, Directional Attenuator     |
| Connector 1               | TNC Female                        |
| Connector 2               | N Female                          |
| Body Material and Plating | Aluminum Heatsink, Black Anodized |

**Electrical Specifications**

|                            |          |
|----------------------------|----------|
| Frequency Range, GHz       | DC to 18 |
| Impedance, Ohms            | 50       |
| Attenuation Value, dB      | 3        |
| Maximum Input Power, Watts | 50       |
| Maximum VSWR               | 1.6:1    |

**Frequency 1**

|                          |         |
|--------------------------|---------|
| Range, GHz               | DC to 6 |
| VSWR                     | 1.3:1   |
| Attenuation Accuracy, dB | 0.75    |

**Frequency 2**

|                          |           |
|--------------------------|-----------|
| Range, GHz               | 6 to 12.4 |
| VSWR                     | 1.45:1    |
| Attenuation Accuracy, dB | 0.75      |

**Frequency 3**

|                          |            |
|--------------------------|------------|
| Range, GHz               | 12.4 to 18 |
| VSWR                     | 1.6:1      |
| Attenuation Accuracy, dB | 1          |

**Mechanical Specifications**

**Temperature**

|                        |             |
|------------------------|-------------|
| Operating Range, deg C | -55 to +125 |
|------------------------|-------------|

**Size**

|                 |                |
|-----------------|----------------|
| Length, in [mm] | 4.01 [101.85]  |
| Width, in [mm]  | 3 [76.2]       |
| Height, in [mm] | 3 [76.2]       |
| Weight, lbs [g] | 1.796 [814.65] |

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [3 dB Fixed Attenuator, TNC Female To N Female Directional Rated To 50 Watts Up To 18 GHz PE7327-3](#)

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal.



3 dB Fixed Attenuator, TNC Female To N Female  
Directional Rated To 50 Watts Up To 18 GHz

TECHNICAL DATA SHEET

PE7327-3

**Connector 1**

|                              |                             |
|------------------------------|-----------------------------|
| Type                         | TNC Female                  |
| Contact Material and Plating | Brass, Gold                 |
| Hex Size, In.                | 11/16                       |
| Body Material and Plating    | Stainless Steel, Passivated |

**Connector 2**

|                                      |                             |
|--------------------------------------|-----------------------------|
| Type                                 | N Female                    |
| Contact Material and Plating         | Brass, Gold                 |
| Outer Conductor Material and Plating | Brass, Silver               |
| Hex Size, In.                        | 11/16                       |
| Body Material and Plating            | Stainless Steel, Passivated |

**Compliance Certifications** (visit [www.Pasternack.com](http://www.Pasternack.com) for current document)

|                |     |
|----------------|-----|
| RoHS Compliant | Yes |
|----------------|-----|

**Plotted and Other Data**

|        |   |
|--------|---|
| Notes: | Values at 25 °C, sea level<br>OUTPUT PORT HANDLES 5 WATTS MAX POWER   |
| URL:   | <a href="http://www.pasternack.com/3db-fixed-tnc-female-n-female-50-watts-attenuator-pe7327-3-p.aspx">http://www.pasternack.com/3db-fixed-tnc-female-n-female-50-watts-attenuator-pe7327-3-p.aspx</a> |

3 dB Fixed Attenuator, TNC Female To N Female Directional Rated To 50 Watts Up To 18 GHz from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and fiber optic products maintain a 99% availability and are part of the broadest selection in the industry.

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal.

# PE7327-3 CAD Drawing

3 dB Fixed Attenuator, TNC Female To N Female  
Directional Rated To 50 Watts Up To 18 GHz

| xx | Input Connector | Output Connector |
|----|-----------------|------------------|
| 10 | 7/16 Female     | 7/16 Male        |
| 11 | N Female        | 7/16 Male        |
| 12 | 7/16 Male       | 7/16 Female      |
| 13 | 7/16 Female     | 7/16 Female      |
| 14 | N Male          | 7/16 Female      |
| 15 | N Female        | 7/16 Female      |
| 16 | 7/16 Female     | N Male           |
| 17 | N Female        | N Male           |
| 18 | SMA Female      | N Male           |
| 19 | TNC Female      | N Male           |
| 20 | 7/16 Male       | N Female         |
| 21 | 7/16 Female     | N Female         |
| 22 | N Male          | N Female         |
| 23 | N Female        | N Female         |
| 24 | SMA Male        | N Female         |
| 25 | SMA Female      | N Female         |
| 26 | TNC Male        | N Female         |
| 27 | TNC Female      | N Female         |
| 28 | 7/16 Female     | SMA Male         |
| 29 | N Female        | SMA Male         |
| 30 | SMA Female      | SMA Male         |
| 31 | TNC Female      | SMA Male         |
| 32 | 7/16 Male       | SMA Female       |
| 33 | 7/16 Female     | SMA Female       |
| 34 | N Male          | SMA Female       |
| 35 | N Female        | SMA Female       |
| 36 | SMA Male        | SMA Female       |
| 37 | SMA Female      | SMA Female       |
| 38 | TNC Male        | SMA Female       |
| 39 | TNC Female      | SMA Female       |
| 40 | 7/16 Female     | TNC Male         |
| 41 | N Female        | TNC Male         |
| 42 | SMA Female      | TNC Male         |
| 43 | TNC Female      | TNC Male         |
| 44 | 7/16 Male       | TNC Female       |
| 45 | 7/16 Female     | TNC Female       |
| 46 | N Male          | TNC Female       |
| 47 | N Female        | TNC Female       |
| 48 | SMA Male        | TNC Female       |
| 49 | SMA Female      | TNC Female       |
| 50 | TNC Male        | TNC Female       |
| 51 | TNC Female      | TNC Female       |

| Connector Type | DIM "A" (REF.) |
|----------------|----------------|
| SMA Male       | 0.68           |
| SMA Female     | 0.54           |
| TNC Male       | 0.98           |
| TNC Female     | 0.94           |
| N Female       | 0.95           |
| N Male         | 0.98           |
| 7/16 Male      | 1.12           |
| 7/16 Female    | 1.16           |



NOTES:  
1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.  
2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.  
3. DIMENSIONS ARE IN INCHES [mm].

DWG TITLE  
**PE73xx-yy**

FSCM NO. 53919

CAD FILE 102512

SCALE N/A

SIZE A

2233

**PE PASTERNAK®**  
Pasternack Enterprises, Inc.  
P.O. Box 16759 | Irvine | CA | 92623  
Phone: (949) 261-1920 | Fax: (949) 261-7451  
Website: www.pasternack.com | E-Mail: sales@pasternack.com