



Low Loss Flexible LMR-500-DB Outdoor/Watertight Rated
Coax Cable Double Shielded with Black PE Jacket

RF Cables
Technical Data Sheet

LMR-500-DB-FT

Times Microwave Systems Coax Cable Specification
Configuration

- Low Loss, Outdoor/Watertight Flexible Cable
- 2 Shield(s)

Features

- Easily Routed
- Low Loss Cable
- RF Shielding > 90dB
- Designed for Outdoor Use
- Watertight

Applications

- Jumper Assemblies
- Short Antenna Feeder Runs
- Wireless Communications

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		5.8	GHz
Impedance		50		Ohms
Velocity of Propagation		86		%
Time Delay		1.18 [3.87]		ns/ft [ns/m]
Shielding Effectiveness	90			dB
Dielectric Withstanding Voltage (DC)			3,000	Vdc
Jacket Spark			8,000	Vrms
Inner Conductor DC Resistance			0.82	Ohms/1000ft
Outer Conductor DC Resistance			1.27	Ohms/1000ft
Nominal Capacitance		23.6 [77.43]		pF/ft [pF/m]
Nominal Inductance		0.059 [0.19]		uH/ft [uH/m]
Input Power (Peak)			22	kWatts

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Low Loss Flexible LMR-500-DB Outdoor/Watertight Rated Coax Cable Double Shielded with Black PE Jacket LMR-500-DB-FT](#)



Low Loss Flexible LMR-500-DB Outdoor/Watertight Rated Coax Cable Double Shielded with Black PE Jacket

RF Cables Technical Data Sheet

LMR-500-DB-FT

Performance by Frequency Band

Description	F1	F2	F3	F4	F5	Units
Frequency	50	150	220	450	900	MHz
Attenuation, Typ	0.7	1.2	1.5	2.2	3.1	dB/100ft
	2.3	3.94	4.92	7.22	10.17	dB/100m
Input Power (CW), Max	3,393	1,931	1,583	1,088	752	Watts

Description	F6	F7	F8	F9	F10	Units
Frequency	1.5	1.8	2	2.5	5.8	GHz
Attenuation, Typ	4.1	4.6	4.8	5.5	8.9	dB/100ft
	13.45	15.09	15.75	18.04	29.2	dB/100m
Input Power (CW), Max	569	515	485	428	264	Watts

Electrical Specification Notes:

Values at 25°C, sea level. // Attenuation = $0.096590 \cdot \sqrt{\text{FMHz}} + 0.000260$

Mechanical Specifications

Diameter	0.5 in [12.7 mm]
Weight	0.103 lbs/ft [0.15 kg/m]
Min. Bend Radius (Installation)	1.25 in [31.75 mm]
Min. Bend Radius (Repeated)	5 in [127 mm]
Bending Moment	1.75 lbs-ft [2.37 N-m]
Tensile Strength	260 lbs [117.93 kg]
Flat Plate Crush	50 lbs/in [0.89 kg/mm]

Construction Specifications

Description	Material and Plating	Diameter
Inner Conductor	Copper Clad Aluminum, 1 Strand	0.142 in [3.61 mm]
Conductor Type	Solid	
Dielectric	PE (F)	0.37 in [9.4 mm]
First Shield	Aluminum Tape	0.376 in [9.55 mm]
Second Shield	Tinned Copper	0.405 in [10.29 mm]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Low Loss Flexible LMR-500-DB Outdoor/Watertight Rated Coax Cable Double Shielded with Black PE Jacket LMR-500-DB-FT](#)



Low Loss Flexible LMR-500-DB Outdoor/Watertight Rated
Coax Cable Double Shielded with Black PE Jacket

RF Cables
Technical Data Sheet

LMR-500-DB-FT

Jacket	PE, Black	0.5 in [12.7 mm]
--------	-----------	------------------

Environmental Specifications

Temperature

Operating Range	-40 to 85 deg C
Installation Range	-40 to 85 deg C
Storage Range	-70 to 85 deg C

Environmental Specification Notes:
Outdoor/Watertight

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Low Loss Flexible LMR-500-DB Outdoor/Watertight Rated Coax Cable Double Shielded with Black PE Jacket from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Low Loss Flexible LMR-500-DB Outdoor/Watertight Rated Coax Cable Double Shielded with Black PE Jacket LMR-500-DB-FT](#)


URL: <https://www.pasternack.com/50-ohm-low-loss-lmr-500-db-pe-jacket-doubleshieldedblack-lmr-500-db-ft-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

LMR-500-DB-FT CAD Drawing

Low Loss Flexible LMR-500-DB Outdoor/Watertight Rated
Coax Cable Double Shielded with Black PE Jacket

REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	03/14/2022	AGANWANI



UNLESS OTHERWISE SPECIFIED
LEADING DIMENSIONS ARE INCHES
DIMENSIONS IN [] ARE MILLIMETERS

TOLERANCES:

X = ± .2	[.008]	FRACTIONS
.XX = ± .02	[.51]	± 1/32
.XXX = ± .005	[.13]	ANGLES ± 1°

CABLE LENGTH (L) TOLERANCES:

L ≤ 12	[305]	= +1 [25] / -0
12 [305] < L ≤ 60	[1524]	= +2 [51] / -0
60 [1524] < L ≤ 120	[3048]	= +4 [102] / -0
120 [3048] < L ≤ 300	[7620]	= +6 [152] / -0
300 [7620] < L		= +5% / -0

ALL DIMENSIONS SHOWN
ARE FOR REFERENCE ONLY.

PE PASTERNAK
an INFINITI® brand

Pasternack Enterprises, Inc.
P.O. Box 16759, Irvine, CA 92623.
Phone: 1.949.261.1920 | 1.866.727.8376
Fax: 1.949.261.7451
Website: www.pasternack.com
E-mail: sales@pasternack.com

THIRD-ANGLE PROJECTION

THE INFORMATION AND
DESIGN IN THIS DOCUMENT
IS THE PROPERTY OF
PASTERNAK CORPORATION
ALL RIGHTS RESERVED.

SHEET 1 OF 1

SCALE N/A

SIZE A

CAGE CODE 53919

DRAWN BY DZINN

ITEM NO. LMR-500-DB-FT

REV A

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE
WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.