



45 dB Gain, 100 Watt Psat, 700 MHz to 2.7 GHz, High Power High Gain Amplifier Class A/AB, GaN, SMA

TECHNICAL DATA SHEET

PE15A5033F

The PE15A5033F is a 100 W high gain Class A/AB GaN Linear Power Amplifier operating in the 0.7 to 2.7 GHz frequency range. The amplifier offers 100 Watts typical saturated power and 45 dB minimum small signal gain with ± 1.5 dB typical gain flatness. The amplifier requires typically a +30V DC power supply. The SMA connectorized module is unconditionally stable and operates over the temperature range of 0°C and +50°C. The unit comes with a Heatsink and Fan.

Features

- 0.7 GHz to 2.7 GHz Frequency Range
- Psat 100 Watts typ
- Small Signal Gain: 45 dB min
- Gain Flatness ± 1.5 dB typ
- Switching Time 5 usec max
- 50 Ohms Input and Output Matched
- Unconditionally Stable
- Regulated Supply
- RF Input Signal Format: CW/AM/FM/Pulse
- Efficiency (PAE) 30% Typical
- Heatsink and Fan

Applications

- Military Radio
- Communication Systems
- High Gain Driver Power Amplifier
- High Gain Output Power Amplifier

Electrical Specifications (TA = +25°C, DC Voltage = 30Volts, DC Current = 8,733mA)

Description	Minimum	Typical	Maximum	Units
Frequency Range	0.7		2.7	GHz
Small Signal Gain	45			dB
Gain Flatness @ Psat		± 1.5	± 2	dB
Input Power (CW)		+7	+10	dBm
Psat	+49.5	+50		dBm
Efficiency (PAE)	25	30		%
Harmonics		-20	-15	dBc
Spurious		-70	-60	dBc
Input VSWR			2:1	
Switching Speed for On/Off Switch Gate			5	usec
TTL Control	"1": On, "0": Off, Enable: 5V, Disable: 0V			
Operating DC Voltage		30		Volts
Operating DC Current		8,733	16,666	mA
DC Consumption		262	500	Watts
Operating Temperature Range	0		+50	°C

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [45 dB Gain, 100 Watt Psat, 700 MHz to 2.7 GHz, High Power High Gain Amplifier Class A/AB, GaN, SMA PE15A5033F](#)



45 dB Gain, 100 Watt Psat, 700 MHz to 2.7 GHz, High Power High Gain Amplifier Class A/AB, GaN, SMA

TECHNICAL DATA SHEET

PE15A5033F

Mechanical Specifications

Size

Length	10.75 in [273.05 mm]
Width	7 in [177.8 mm]
Height	3.75 in [95.25 mm]
Weight	9.277 lbs [4.21 Kg]
Input Connector	SMA Female
Output Connector	SMA Female
Cooling	Adequate Airflow Required

Environmental Specifications

Temperature

Operating Range	0 to +50 deg C
Humidity	95% Non-Condensing
Shock	Normal Truck Transport
Vibration	Normal Truck Transport
Altitude	10000 feet Above Sea Level

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

- Values at +25 °C, sea level
- ESD Sensitive Material, Transport material in Approved ESD bags. Handle only in approved ESD Workstation.



Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [45 dB Gain, 100 Watt Psat, 700 MHz to 2.7 GHz, High Power High Gain Amplifier Class A/AB, GaN, SMA PE15A5033F](#)





45 dB Gain, 100 Watt Psat, 700 MHz to 2.7 GHz, High Power High Gain Amplifier Class A/AB, GaN, SMA

TECHNICAL DATA SHEET

PE15A5033F

Typical Performance Data




Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [45 dB Gain, 100 Watt Psat, 700 MHz to 2.7 GHz, High Power High Gain Amplifier Class A/AB, GaN, SMA PE15A5033F](#)



45 dB Gain, 100 Watt Psat, 700 MHz to 2.7 GHz, High Power High Gain Amplifier Class A/AB, GaN, SMA

TECHNICAL DATA SHEET

PE15A5033F





Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [45 dB Gain, 100 Watt Psat, 700 MHz to 2.7 GHz, High Power High Gain Amplifier Class A/AB, GaN, SMA PE15A5033F](#)



45 dB Gain, 100 Watt Psat, 700 MHz to 2.7 GHz, High Power High Gain Amplifier Class A/AB, GaN, SMA

TECHNICAL DATA SHEET

PE15A5033F



Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [45 dB Gain, 100 Watt Psat, 700 MHz to 2.7 GHz, High Power High Gain Amplifier Class A/AB, GaN, SMA PE15A5033F](#)



45 dB Gain, 100 Watt Psat, 700 MHz to 2.7 GHz, High Power High Gain Amplifier Class A/AB, GaN, SMA

TECHNICAL DATA SHEET

PE15A5033F

45 dB Gain, 100 Watt Psat, 700 MHz to 2.7 GHz, High Power High Gain Amplifier Class A/AB, GaN, SMA from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.


Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [45 dB Gain, 100 Watt Psat, 700 MHz to 2.7 GHz, High Power High Gain Amplifier Class A/AB, GaN, SMA PE15A5033F](https://www.pasternack.com/45-db-gain-100-watt-psat-700-mhz-to-2.7-ghz-high-power-high-gain-amplifier-class-a-ab-gan-sma-pe15a5033f)

URL: <https://www.pasternack.com/45-db-gain-2.7-ghz-high-power-high-gain-amplifier-sma-pe15a5033f-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PE15A5033F CAD Drawing

45 dB Gain, 100 Watt Psat, 700 MHz to 2.7 GHz, High Power
High Gain Amplifier Class A/AB, GaN, SMA



NOTE:
HEAT SINK REQUIRED FOR PROPER OPERATION,
UNIT IS COOLED BY CONDUCTING TO HEAT SINK.

DWG TITLE

PE15A5033F

NOTES:
1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.
2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.
3. DIMENSIONS ARE IN INCHES [mm].

PASTERNAK
THE ENGINEER'S RF SOURCE
Pasternack Enterprises, Inc.
P.O. Box 16759 | Irvine | CA | 92623
Phone: (949) 261-1920 | Fax: (949) 261-7451
Website: www.pasternack.com | E-Mail: sales@pasternack.com

FSCM NO. 53919

CAD FILE 052015


SCALE N/A

SIZE A

2233

PE15A5033F CAD Drawing

45 dB Gain, 100 Watt Psat, 700 MHz to 2.7 GHz, High Power
High Gain Amplifier Class A/AB, GaN, SMA



View A

View B


NOTES:
1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.
2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.
3. DIMENSIONS ARE IN INCHES [mm].

DWG TITLE	PE15A5033F		
FSCM NO.	53919	CAD FILE	052015
SCALE	N/A	SIZE	A
			2233

PE PASTERNAK
THE ENGINEER'S RF SOURCE
Pasternack Enterprises, Inc.
P.O. Box 16759 | Irvine | CA | 92623
Phone: (949) 261-1920 | Fax: (949) 261-7451
Website: www.pasternack.com | E-Mail: sales@pasternack.com

PE15A5033F CAD Drawing

45 dB Gain, 100 Watt Psat, 700 MHz to 2.7 GHz, High Power
High Gain Amplifier Class A/AB, GaN, SMA



NOTES:
1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.
2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.
3. DIMENSIONS ARE IN INCHES [mm].

DWG TITLE
PE15A5033F

PE PASTERNAK
THE ENGINEER'S RF SOURCE
Pasternack Enterprises, Inc.
P.O. Box 16759 | Irvine | CA | 92623
Phone: (949) 261-1920 | Fax: (949) 261-7451
Website: www.pasternack.com | E-Mail: sales@pasternack.com

FSCM NO. 53919

CAD FILE 052015

SCALE N/A

SIZE A

2233