



2 Way SMA Power Divider From 8 GHz to 18 GHz Rated at 10 Watts

Power Dividers Technical Data Sheet

PE2027

Features

- 2-Way Power Divider
- Wilkinson Design
- 8 to 18 GHz Frequency Range
- Max Power 10 Watts (CW)
- Insertion Loss < 0.6 dB
- Isolation > 20 dB

Applications

- Test and Measurement
- Military Communications
- Commercial Communications
- Wireless Communications
- SATCOM

Description

Pasternack carries a wide selection of power dividers to fit your needs. These components are essential in many systems, allowing the combination of multiple signals or splitting of a single signal into multiple signals with equal magnitude and phase. Pasternack's resistive and Wilkinson power dividers come with excellent performance featuring minimal loss, high isolation and low VSWR. They are available in both narrow and broad bandwidths with a variety of connector types such as 2.92mm, BNC, N and SMA.

The PE2027 is a 2-way Wilkinson power divider that operates from 8 to 18 GHz and can handle up to 10 Watts (CW) with 0.6 dB max insertion loss and 20 dB min isolation. The package interface uses SMA female connectors and is REACH and RoHS compliant.

Electrical Specifications

Design	Wilkinson
Number of Output Ports	2

Description	Minimum	Typical	Maximum	Units
Frequency Range	8		18	GHz
Impedance		50		Ohms
Insertion Loss			0.6	dB
Amplitude Balance			0.3	dB
Phase Balance			5	Degrees
Input Power (CW)			10	Watts

Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency Range	8 to 12.4	12.4 to 18				GHz
Input VSWR, Max	1.4:1	1.5:1				
Isolation, Min	20	18				dB

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [2 Way SMA Power Divider From 8 GHz to 18 GHz Rated at 10 Watts PE2027](#)



2 Way SMA Power Divider From 8 GHz to 18 GHz Rated at 10 Watts

Power Dividers Technical Data Sheet

PE2027

Mechanical Specifications

Size

Length	1 in [25.4 mm]
Width	1 in [25.4 mm]
Height	0.5 in [12.7 mm]
Weight	0.074 lbs [33.57 g]

Configuration

Package Type	Connectorized
Input Connector	SMA Female
Input Connector Specification	MIL-STD-348
Output Connectors	SMA Female
Output Connectors Specification	MIL-STD-348

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

2 Way SMA Power Divider From 8 GHz to 18 GHz Rated at 10 Watts from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.


Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [2 Way SMA Power Divider From 8 GHz to 18 GHz Rated at 10 Watts PE2027](#)

URL: <https://www.pasternack.com/4-way-sma-reactive-power-divider-8-ghz-18-ghz-10-watts-pe2027-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PE2027 CAD Drawing

2 Way SMA Power Divider From 8 GHz to 18 GHz Rated at 10 Watts



STANDARD TOLERANCES

DECIMAL ±0.01

.XX ±0.005

.XXX ±0.005

*STANDARD TOLERANCES APPLY ONLY TO DIMENSIONS IN INCHES

PE PASTERNAK
THE ENGINEER'S RF SOURCE

Pasternack Enterprises, Inc.
P.O. Box 16759 | Irvine | CA | 92623
Phone: (949) 261-1920 | Fax: (949) 261-7451
Website: www.pasternack.com | E-Mail: sales@pasternack.com

DWG TITLE

PE2027

NOTES:
1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.
2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.
3. DIMENSIONS ARE IN INCHES [mm].

FSCM NO. 53919

CAD FILE 050516

SCALE N/A

SIZE A

3045