

3 Way BNC Wilkinson Power Divider From 2 MHz to 200 MHz Rated at 1 Watt



Power Dividers Technical Data Sheet

PE2007

Features

- 3-Way Power Divider
- Wilkinson Design
- 2 to 200 MHz Frequency Range

- Max Power 1 Watt (CW)
- Insertion Loss < 1 dB
- Isolation > 20 dB

Applications

- Test and Measurement
- Military Communications
- Commercial Communications
- · Wireless Communications
- SATCOM

Description

Pasternack carries a wide selection of power dividers to fit your needs. These components are essential in many systems, allowing the combination of multiple signals or splitting of a single signal into multiple signals with equal magnitude and phase. Pasternack's resistive and Wilkinson power dividers come with excellent performance featuring minimal loss, high isolation and low VSWR. They are available in both narrow and broad bandwidths with a variety of connector types such as 2.92mm, BNC, N and SMA.

The PE2007 is a 3-way Wilkinson power divider that operates from 2 to 200 MHz and can handle up to 1 Watt (CW) with 1 dB max insertion loss and 20 dB min isolation. The package interface uses BNC female connectors and is REACH and RoHS compliant.

Electrical Specifications

Design Wilkinson
Number of Output Ports 3

Description	Minimum	Typical	Maximum	Units
Frequency Range	2		200	MHz
Impedance		50		Ohms
Input VSWR			1.35:1	
Output VSWR			1.35:1	
Insertion Loss			1	dB
Isolation	20			dB
Input Power (CW)			1	Watts

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: 3 Way BNC Wilkinson Power Divider From 2 MHz to 200 MHz Rated at 1 Watt PE2007

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com



3 Way BNC Wilkinson Power Divider From 2 MHz to 200 MHz Rated at 1 Watt



Power Dividers Technical Data Sheet

PE2007

Mechanical Specifications

Size

 Length
 1.87 in [47.5 mm]

 Width
 1.4 in [35.56 mm]

 Height
 0.62 in [15.75 mm]

 Weight
 0.137 lbs [62.14 g]

Configuration

Package Type Connectorized
Input Connector BNC Female
Input Connector Specification MIL-STD-348
Output Connectors BNC Female
Output Connectors Specification MIL-STD-348

Environmental Specifications

Temperature

Operating Range -30 to +70 deg C

Compliance Certifications (visit www.Pasternack.com for current document)

RoHS Compliant REACH Compliant

EACH Compliant 12/17/2015

Plotted and Other Data

Notes:

3 Way BNC Wilkinson Power Divider From 2 MHz to 200 MHz Rated at 1 Watt from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: 3 Way BNC Wilkinson Power Divider From 2 MHz to 200 MHz Rated at 1 Watt PE2007

URL: http://www.pasternack.com/3-way-bnc-reactive-power-divider-2-mhz-200-mhz-1-watts-pe2007-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 Phone: (866) 727-8376 or (949) 261-1920 • Fax: (949) 261-7451

PE2007 CAD Drawing

3 Way BNC Wilkinson Power Divider From 2 MHz to 200 MHz Rated at 1 Watt

