

N Male to HN Male Cable Using RG213 Coax




PE3125

Configuration

- Connector 1: N Male
- Connector 2: HN Male
- Cable Type: RG213
- Coax Flex Type: Flexible

Features

- Max Frequency 1 GHz
- 66% Phase Velocity
- PVC Jacket



Applications

- General Purpose
- Laboratory Use

Description

Pasternack's PE3125 type N male to HN male cable using RG213 coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack type N to HN cable assembly has a male to male gender configuration with 50 ohm flexible RG213 coax. The PE3125 type N male to HN male cable assembly operates to 1 GHz.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		1,000	MHz
VSWR			1.4:1	
Velocity of Propagation		66		%
Capacitance		30.8 [101.05]		pF/ft [pF/m]
Operating Voltage (AC)			1,000	Vrms

Specifications by Frequency



N Male to HN Male Cable Using RG213 Coax

PE3125

Part Number	Length	Description	F1	F2	F3	F4	F5	Units	Weight (lbs)
		Frequency	50	100	250	500	1000	MHz	
PE3125	Custom Lengths Available	Insertion Loss (Typ.)	0.011	0.022	0.035	0.053	0.08	dB/ft	
			0.04	0.08	0.12	0.18	0.27	dB/m	
PE3125-24	24 inch	Insertion Loss (Typ.)	0.23	0.25	0.27	0.31	0.36	dB	0.388
PE3125-36	36 inch	Insertion Loss (Typ.)	0.24	0.27	0.31	0.36	0.44	dB	0.489
PE3125-48	48 inch	Insertion Loss (Typ.)	0.25	0.29	0.34	0.42	0.52	dB	0.59
PE3125-60	60 inch	Insertion Loss (Typ.)	0.26	0.31	0.38	0.47	0.6	dB	0.691
PE3125-72	72 inch	Insertion Loss (Typ.)	0.27	0.34	0.41	0.52	0.68	dB	0.792

The insertion loss data for the base model does not include loss due to the connectors. Each length includes insertion loss due to the connectors.

Loss due to Connector 1: 0.1 dB
 Loss due to Connector 2: 0.1 dB
 Base Weight: 0.286 pounds
 Additional Weight per Inch: 0.00842 pounds

Mechanical Specifications

Cable Assembly

Weight 0.286 lbs [129.73 g]

Cable

Cable Type RG213
 Impedance 50 Ohms
 Inner Conductor Type Stranded
 Inner Conductor Material and Plating Copper
 Dielectric Type PE
 Number of Shields 1
 Shield Layer 1 Copper Braid
 Jacket Material PVC, Black
 Jacket Diameter 0.405 in [10.29 mm]
 Repeated Minimum Bend Radius 1.6 in [40.64 mm]

N Male to HN Male Cable Using RG213 Coax



PE3125

Connectors

Description	Connector 1	Connector 2
Type	N Male	HN Male
Specification	MIL-STD-348A	MIL-STD-348A
Impedance	50 Ohms	50 Ohms
Configuration	Straight	Straight
Contact Material and Plating	Brass, Gold	Brass, Gold
Contact Plating Specification	30 µin minimum	30µ in. minimum
Dielectric Type	PTFE	PTFE
Body Material and Plating	Brass, Nickel	Brass, Nickel
Body Plating Specification	100 µin minimum	100µ in. minimum
Coupling Nut Material and Plating	Brass, Nickel	Brass, Nickel
Coupling Nut Plating Specification	100 µin minimum	100µ in. minimum

Environmental Specifications

Operating Range Temperature -25 to +70 deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

N Male to HN Male Cable Using RG213 Coax



PE3125

Typical Performance Data

How to Order

Part Number Configuration:

PE3125

- xx

uu

Unit of Measure:
cm = Centimeters
<blank> = Inches

Length

Base Number

Example: PE3125-12 = 12 inches long cable
PE3125-100cm = 100 cm long cable

N Male to HN Male Cable Using RG213 Coax from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [N Male to HN Male Cable Using RG213 Coax PE3125](#)

URL: <https://www.pasternack.com/n-male-to-hn-male-cable-using-rg213-pe3125-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

