



TNC Male to TNC Male Cable 36 Inch Length Using RG402 Coax

RF Cable Assemblies Technical Data Sheet

PE3074-36

Configuration

- Connector 1: TNC Male
- Connector 2: TNC Male
- Cable Type: RG402

Features

- Max Frequency 6 GHz
- 69.5% Phase Velocity

Applications

- General Purpose
- Laboratory Use

Description

Pasternack's PE3074-36 TNC male to TNC male 36 inch cable using RG402 coax is part of our full line of RF components available for same-day shipping. Pasternack's semi-rigid RF cable assemblies are ideal for high performance applications and can be formed, using proper tooling, to the routing pattern required. This Pasternack TNC to TNC cable assembly has a male to male gender configuration with 50 ohm semi-rigid RG402 coax. The PE3074-36 TNC male to TNC male cable assembly operates to 6 GHz.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

| Description | Minimum | Typical | Maximum | Units |
|-------------------------|---------|---------|---------|-------|
| Frequency Range | DC | | 6 | GHz |
| VSWR | | | 1.5:1 | |
| Velocity of Propagation | | 69.5 | | % |

Specifications by Frequency

| Description | F1 | F2 | F3 | F4 | F5 | Units |
|-----------------------|-------|-------|-------|-------|-------|-------|
| Frequency | 0.25 | 0.5 | 1 | 2.5 | 6 | GHz |
| Insertion Loss (Max.) | 0.314 | 0.428 | 0.533 | 0.724 | 1.135 | dB |

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [TNC Male to TNC Male Cable 36 Inch Length Using RG402 Coax PE3074-36](#)



TNC Male to TNC Male Cable 36 Inch Length Using RG402 Coax

RF Cable Assemblies Technical Data Sheet

PE3074-36

Mechanical Specifications

Cable Assembly

| | |
|----------|---------------------|
| Length* | 36 in [914.4 mm] |
| Diameter | 0.571 in [14.5 mm] |
| Weight | 0.173 lbs [78.47 g] |

Cable

| | |
|--------------------------------------|---------------------------|
| Cable Type | RG402 |
| Impedance | 50 Ohms |
| Inner Conductor Type | Solid |
| Inner Conductor Material and Plating | Copper Clad Steel, Silver |
| Dielectric Type | PTFE |
| Number of Shields | 1 |
| Outer Conductor Material and Plating | Copper |
| Repeated Minimum Bend Radius | 0.25 in [6.35 mm] |

Connectors

| Description | Connector 1 | Connector 2 |
|------------------------------------|-----------------|-----------------|
| Type | TNC Male | TNC Male |
| Specification | MIL-STD-348A | MIL-STD-348A |
| Impedance | 50 Ohms | 50 Ohms |
| Contact Material and Plating | Brass, Gold | Brass, Gold |
| Contact Plating Specification | 50 µin minimum | 50 µin minimum |
| Dielectric Type | PTFE | PTFE |
| Body Material and Plating | Brass, Gold | Brass, Gold |
| Body Plating Specification | 30 µin minimum | 30 µin minimum |
| Coupling Nut Material and Plating | Brass, Nickel | Brass, Nickel |
| Coupling Nut Plating Specification | 100 µin minimum | 100 µin minimum |

Environmental Specifications

Temperature

| | |
|-----------------|-------------------|
| Operating Range | -55 to +125 deg C |
|-----------------|-------------------|

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

- Values at 25°C, sea level.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [TNC Male to TNC Male Cable 36 Inch Length Using RG402 Coax PE3074-36](#)



TNC Male to TNC Male Cable 36 Inch Length Using RG402 Coax

RF Cable Assemblies Technical Data Sheet

PE3074-36

How to Order

Part Number Configuration:

PE3074

- **xx**

uu

Unit of Measure:
cm = Centimeters
<blank> = Inches
Length
Base Number

Example: PE3074-12 = 12 inches long cable
PE3074-100cm = 100 cm long cable

TNC Male to TNC Male Cable 36 Inch Length Using RG402 Coax from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [TNC Male to TNC Male Cable 36 Inch Length Using RG402 Coax PE3074-36](#)


URL: <https://www.pasternack.com/tnc-male-tnc-male-rg402u-cable-assembly-pe3074-36-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PE3074-36 CAD Drawing

TNC Male to TNC Male Cable 36 Inch Length Using RG402 Coax

| Standard Lengths | |
|------------------|-------------------------|
| -12 | 12" |
| -24 | 24" |
| -36 | 36" |
| -48 | 48" |
| -60 | 60" |
| -XXX | Custom Length in Inches |



DWG TITLE

PE3074-XX

NOTES:

- 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.
- 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.
- 3. DIMENSIONS ARE IN INCHES (mm).
- 4. LENGTH TOLERANCE IS $\pm 1.5\%$ OR $3/8"$, WHICHEVER IS GREATER.



Pasternack Enterprises, Inc.
P.O. Box 16759 | Irvine | CA | 92623
Phone: (949) 261-1920 | Fax: (949) 261-7451
Website: www.pasternack.com | E-Mail: sales@pasternack.com

REV. -

FSCM NO. 53919

CAD FILE 020907

SCALE N/A

SIZE A

127