

PASTERNASK

SMA Male to Push-On SMA Male Precision Cable 60 Inch Length Using 160 Series Coax, RoHS

TECHNICAL DATA SHEET

PE311-60

Configuration

Connector 1 SMA Male
Connector 2 SMA Male
Cable Type 160 Series

Electrical Specifications

Frequency Range DC to 18 GHz
Impedance 50 Ohms
Maximum VSWR 1.38:1
Velocity of Propagation 70 %
Dielectric Withstanding Voltage (AC) 1,000 Vrms

Typical Performance by Frequency

Frequency 1

 Frequency
 2 GHz

 VSWR
 1.09:1

 Return Loss
 27 dB

Insertion Loss 0.35 dB/ft [1.15 dB/m]

Frequency 2

 Frequency
 6 GHz

 VSWR
 1.12:1

 Return Loss
 25 dB

 Insertion Loss
 0.6 dB/ft [1.97 dB/m]

Frequency 3

Frequency 8 GHz VSWR 1.17:1 Return Loss 22 dB

Insertion Loss 0.7 dB/ft [2.3 dB/m]

Frequency 4

Frequency 18 GHz VSWR 1.38:1 Return Loss 16 dB

Insertion Loss 1.175 dB/ft [3.85 dB/m]

Mechanical Specifications

Temperature

Temperature Operating Range -55 to +125 deg C

Size

 Length
 60 in [152.4 cm]

 Diameter
 0.17 in [4.32 mm]

 Weight
 0.038 lbs [17.24 g]

Cable Color Blue

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: SMA Male to Push-On SMA Male Precision Cable 60 Inch Length Using 160 Series Coax, RoHS PE311-60

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com



PASTERNASK

SMA Male to Push-On SMA Male Precision Cable 60 Inch Length Using 160 Series Coax, RoHS

TECHNICAL DATA SHEET

PE311-60

One Time Minimum Bend Radius 1 in [25.4 mm]

Cable

Cable Type160 SeriesNo of Shields3Dielectric TypePTFEJacket MaterialFEP

Jacket Diameter 0.163 in [4.14 mm]

Connector 1

Type SMA Male
Configuration Straight
Mating Cycles 500
Inner Conductor Material and Plating Gold

Coupling Nut Material and Plating

Passivated Stainless Steel

Hex Size 5/16 in.

Torque 8 in-lbs [0.9 Nm]

Body Material and Plating Gold
Dielectric Type PTFE

Connector 2

Type SMA Male
Configuration Straight
Mating Cycles 500
Inner Conductor Material and Plating Gold
Outer Conductor Material and Plating Gold
Body Material and Plating Gold
Dielectric Type PTFE

Compliance Certifications (visit www.Pasternack.com for current document)

RoHS Compliant Yes
REACH Compliant 12/19/2011

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: SMA Male to Push-On SMA Male Precision Cable 60 Inch Length Using 160 Series Coax, RoHS PE311-60

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com



SMA Male to Push-On SMA Male Precision Cable 60 Inch Length Using 160 Series Coax, RoHS



TECHNICAL DATA SHEET

PE311-60

Plotted and Other Data

Notes:

• Values at +25 °C, sea level

SMA Male to Push-On SMA Male Precision Cable 60 Inch Length Using 160 Series Coax, RoHS from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: SMA Male to Push-On SMA Male Precision Cable 60 Inch Length Using 160 Series Coax, RoHS PE311-60

URL: http://www.pasternack.com/sma-male-sma-male-300-series-cable-assembly-pe311-60-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone**: (866) 727-8376 or (949) 261-1920 • **Fax**: (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com

PE311-60 CAD DrawingSMA Male to Push-On SMA Male Precision Cable 60 Inch Length Using 160 Series Coax, RoHS

