

HN Male Right Angle to N Male Cable Using RG214 Coax with HeatShrink




PE33065/HS

Configuration

- Connector 1: HN Male Right Angle
- Connector 2: N Male
- Cable Type: RG214
- Coax Flex Type: Flexible

Features

- Max Frequency 3 GHz
- 66% Phase Velocity
- Double Shielded
- PVC Jacket



Applications

- General Purpose
- Laboratory Use

Description

Pasternack's PE33065/HS HN male right angle to type N male cable using RG214 coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack HN to type N cable assembly has a male to male gender configuration with 50 ohm flexible RG214 coax. The PE33065/HS HN male to type N male cable assembly operates to 3 GHz. The right angle HN interface on the RG214 cable allows for easier connections in tight spaces. The double shielding of this Pasternack cable assembly provides excellent shielding effectiveness.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		3	GHz
VSWR			1.4:1	
Velocity of Propagation		66		%
Capacitance		30.8 [101.05]		pF/ft [pF/m]
Operating Voltage (AC)			1,000	Vrms

Specifications by Frequency

HN Male Right Angle to N Male Cable
Using RG214 Coax with HeatShrink



PE33065/HS

Part Number	Length	Description	F1	F2	F3	F4	F5	Units	Weight (lbs)
			Frequency					MHz	
PE33065/HS	Custom Lengths Available	Insertion Loss (Typ.)	0.021	0.03	0.046	0.077	0.142	dB/ft	
			0.07	0.1	0.16	0.26	0.47	dB/m	
PE33065/HS-12	12 inch	Insertion Loss (Typ.)	0.32	0.33	0.33	0.35	0.41	dB	0.402
PE33065/HS-36	36 inch	Insertion Loss (Typ.)	0.34	0.37	0.39	0.44	0.63	dB	0.659
PE33065/HS-48	48 inch	Insertion Loss (Typ.)	0.36	0.39	0.42	0.49	0.74	dB	0.787
PE33065/HS-72	72 inch	Insertion Loss (Typ.)	0.38	0.43	0.48	0.58	0.96	dB	1.043
PE33065/HS-108	108 inch	Insertion Loss (Typ.)	0.42	0.49	0.57	0.72	1.29	dB	1.427

The insertion loss data for the base model does not include loss due to the connectors. Each length includes insertion loss due to the connectors.

Loss due to Connector 1: 0.2 dB
 Loss due to Connector 2: 0.1 dB
 Base Weight: 0.402 pounds
 Additional Weight per Inch: 0.01067 pounds

Mechanical Specifications

Cable Assembly

Weight 0.402 lbs [182.34 g]

Cable

Cable Type RG214
 Impedance 50 Ohms
 Inner Conductor Type Stranded
 Inner Conductor Material and Plating Copper, Silver
 Dielectric Type PE
 Number of Shields 2
 Shield Layer 1 Silver Plated Copper Braid
 Shield Layer 2 Silver Plated Copper Braid
 Jacket Material PVC, Black
 Jacket Diameter 0.425 in [10.8 mm]
 Repeated Minimum Bend Radius 1.6 in [40.64 mm]

HN Male Right Angle to N Male Cable
Using RG214 Coax with HeatShrink



PE33065/HS

Connectors

Description	Connector 1	Connector 2
Type	HN Male Right Angle	N Male
Specification	MIL-STD-348A	MIL-STD-348A
Impedance	50 Ohms	50 Ohms
Configuration	Right Angle	Straight
Contact Material and Plating	Brass, Gold	Brass, Gold
Contact Plating Specification	30 µin minimum	30 µin minimum
Dielectric Type	PTFE	PTFE
Body Material and Plating	Brass, Nickel	Brass, Nickel
Body Plating Specification	100 µin minimum	100 µin minimum
Coupling Nut Material and Plating	Brass, Nickel	Brass, Nickel
Coupling Nut Plating Specification	100 µin minimum	100 µin minimum

Environmental Specifications

Operating Range Temperature -20 to +80 deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

HN Male Right Angle to N Male Cable Using RG214 Coax with HeatShrink



PE33065/HS

Typical Performance Data

How to Order

Part Number Configuration:

PE33065/HS - xx uu

Unit of Measure:
cm = Centimeters
<blank> = Inches

Length

Base Number

Example: PE33065/HS-12 = 12 inches long cable
PE33065/HS-100cm = 100 cm long cable

HN Male Right Angle to N Male Cable Using RG214 Coax with HeatShrink from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [HN Male Right Angle to N Male Cable Using RG214 Coax with HeatShrink PE33065/HS](#)

URL: <https://www.pasternack.com/hn-male-right-angle-to-n-male-cable-using-rg214-with-heatshrink-pe33065-hs-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

PE33065/HS CAD Drawing

HN Male Right Angle to N Male Cable Using RG214 Coax with HeatShrink

