

SMA Male Right Angle to TNC Female Bulkhead Cable 60 Inch Length Using RG316 Coax



RF Cable Assemblies Technical Data Sheet

PE33073-60

Configuration

- Connector 1: SMA Male Right Angle
- Connector 2: TNC Female Bulkhead
- Cable Type: RG316

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		3	GHz
VSWR			1.4:1	
Capacitance		32 [104.99]		pF/ft [pF/m]
		02[104.00]	_	pi /it [pi

Specifications by Frequency

F1	F2	F3	F4	F5	Units
0.1	0.25	0.5	1	3	GHz
0.75	1	1.392	2.1	3.1	dB
1.4:1	1.4:1	1.4:1	1.4:1		
15.56	15.563	15.563	15.563		dB
	0.1 0.75 1.4:1	0.1 0.25 0.75 1 1.4:1 1.4:1	0.1 0.25 0.5 0.75 1 1.392 1.4:1 1.4:1 1.4:1	0.1 0.25 0.5 1 0.75 1 1.392 2.1 1.4:1 1.4:1 1.4:1 1.4:1	0.1 0.25 0.5 1 3 0.75 1 1.392 2.1 3.1 1.4:1 1.4:1 1.4:1 1.4:1

Mechanical Specifications

Cable Assembly Length Diameter

Weight

Cable

Cable Type Impedance Inner Conductor Type Inner Conductor Material and Plating Dielectric Type Number of Shields Shield Layer 1 60 in [152.4 cm] 0.689 in [17.5 mm] 0.07 lbs [31.75 g]

RG316 50 Ohms Stranded Copper Clad Steel, Silver PTFE 1 Silver Plated Copper Braid

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: SMA Male Right Angle to TNC Female Bulkhead Cable 60 Inch Length Using RG316 Coax PE33073-60

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 Phone: (866) 727-8376 or (949) 261-1920 • Fax: (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com



SMA Male Right Angle to TNC Female Bulkhead Cable 60 Inch Length Using RG316 Coax

RF Cable Assemblies Technical Data Sheet

Jacket Material Jacket Diameter

FEP, Tan 0.098 in [2.49 mm]

Connectors

Description	Connector 1	Connector 2	
•			
Туре	SMA Male Right Angle	TNC Female Bulkhead	
Specification	MIL-STD-348A	MIL-STD-348A	
Impedance	50 Ohms	50 Ohms	
Contact Material and Plating	Brass, Gold	Brass, Gold	
Contact Plating Specification	50µ in. minimum	30µ in. minimum	
Dielectric Type	Teflon	Teflon	
Hex Size	5/16 in		
Torque	5 in-lbs [0.57 Nm]		
Body Material and Plating	Brass, Nickel	Brass, Nickel	
Body Plating Specification	100µ in. minimum	100µ in. minimum	

Compliance Certifications (visit www.Pasternack.com for current document)

RoHS Compliant **REACH Compliant**

Yes 06/18/2012

Plotted and Other Data

Notes:

• Values at 25°C, sea level.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: SMA Male Right Angle to TNC Female Bulkhead Cable 60 Inch Length Using RG316 Coax PE33073-60

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 Phone: (866) 727-8376 or (949) 261-1920 • Fax: (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com



PE33073-60




SMA Male Right Angle to TNC Female Bulkhead Cable 60 Inch Length Using RG316 Coax



RF Cable Assemblies Technical Data Sheet

PE33073-60



Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 Phone: (866) 727-8376 or (949) 261-1920 • Fax: (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com

PE33073-60 CAD Drawing SMA Male Right Angle to TNC Female Bulkhead Cable 60 Inch Length Using RG316 Coax

