

CO RNA Comment

PE33231-12

SMA Male to N Male Precision Cable 12 Inch Length Using 150 Series Coax, RoHS

TECHNICAL DATA SHEET

SMA Male to N Male Precision Cable 12 Inch	Length Using 150 Series Coax, RoHS
Configuration	
Connector 1	SMA Male
Connector 2	N Male
Cable Type	150 Series
Electrical Specifications	
Frequency Range, GHz	DC to 18
Impedance, Ohms	50
Maximum VSWR	1.4:1
Velocity of Propagation, %	69.5
RF Shielding, dB	90
Maximum Operating Voltage, Vrms	1,900
Typical Electrical Specifications	
Frequency 1	
Frequency, GHz	2
VSWR	1.1:1
Insertion Loss	0.22 dB/ft [0.72 dB/m]
Frequency 2	
Frequency, GHz	6
VSWR	1.08:1
Insertion Loss	0.34 dB/ft [1.12 dB/m]
Frequency 3	
Frequency, GHz	10
VSWR	1.17:1
Insertion Loss	0.45 dB/ft [1.48 dB/m]
Frequency 4	
Frequency, GHz	14
VSWR	1.23:1
Insertion Loss	0.57 dB/ft [1.87 dB/m]
Frequency 5	
Frequency, GHz	18
VSWR	1.25:1
Insertion Loss	0.68 dB/ft [2.23 dB/m]
Electrical Specification Notes:	Short lengths up to 24" long may exhibit VSWR measurements up to 9% higher.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: SMA Male to N Male Precision Cable 12 Inch Length Using 150 Series Coax, RoHS PE33231-12

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal.

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451 Sales@Pasternack.com • Techsupport@Pasternack.com



SMA Male to N Male Precision Cable 12 Inch Length Using 150 Series Coax, RoHS

TECHNICAL DATA SHEET

RNAC	

PE33231-12

Mechanical Specifications Cable Assembly	
Cable Type	150
Temperature Temperature Operating Range, deg C	-55
Size Length, in [mm]	12 [:
One Time Minimum Bend Radius, in [mm]	1 [2
Cable Center Conductor Type Cable Inner Conductor No of Shields Dielectric Type Jacket Material	Solid Cop 1 PTF FEP

Connector 1

Jacket Diameter, in [mm]

Type Configuration Inner Conductor Material and Plating Coupling Nut Material and Plating Hex Size, in. Torque, in-lbs [Nm] Body Material and Plating Dielectric Type

Connector 2

Type Configuration Inner Conductor Material and Plating Outer Conductor Material and Plating Coupling Nut Material and Plating Body Material and Plating Dielectric Type 150 Series 55 to +205

12 [304.8] 1 [25.4]

Solid Copper Clad Steel, Silver 1 PTFE FEP 0.15 [3.81]

SMA Male Straight Copper Clad Steel, Silver Passivated Stainless Steel 5/16 8 [0.9] Passivated Stainless Steel PTFE

N Male Straight Gold Passivated Stainless Steel Brass, Nickel Passivated Stainless Steel PTFE

Compliance Certifications (visit www.Pasternack.com for current document) RoHS Compliant Yes

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: SMA Male to N Male Precision Cable 12 Inch Length Using 150 Series Coax, RoHS PE33231-12

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal.

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451 Sales@Pasternack.com • Techsupport@Pasternack.com



SMA Male to N Male Precision Cable 12 Inch Length Using 150 Series Coax, RoHS

TECHNICAL DATA SHEET

PE33231-12

Plotted and Other Data Notes:

Values at 25 °C, sea level

SMA Male to N Male Precision Cable 12 Inch Length Using 150 Series Coax, RoHS from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and fiber optic products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: SMA Male to N Male Precision Cable 12 Inch Length Using 150 Series Coax, RoHS PE33231-12

URL: http://www.pasternack.com/sma-male-n-male-150-series-cable-assembly-pe33231-12-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal.

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451 Sales@Pasternack.com • Techsupport@Pasternack.com

PE33231-12 CAD Drawing SMA Male to N Male Precision Cable 12 Inch Length Using 150 Series Coax, RoHS

