

## SMA Female Bulkhead to SMB Plug Right Angle Cable Using RG188 Coax with HeatShrink, LF Solder





### PE3336LF/HS

#### Configuration

- Connector 1: SMA Female Bulkhead
- Connector 2: SMB Plug Right Angle
- Cable Type: RG188
- Coax Flex Type: Flexible

#### Features

- PTFE Jacket



#### Applications

- General Purpose
- Laboratory Use

#### Description

Pasternack's PE3336LF/HS SMA female bulkhead to SMB plug right angle cable using RG188 coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack SMA to SMB cable assembly has a female to plug gender configuration with 50 ohm flexible RG188 coax. The right angle SMB interface on the RG188 cable allows for easier connections in tight spaces. Our RF cable assembly with SMA bulkhead interface allows designers to create external connections on their product enclosures, and can be used in a variety of other rack mount and panel mount applications.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

#### Mechanical Specifications

##### Cable Assembly

Weight 0.031 lbs [14.06 g]

##### Cable

Cable Type	RG188
Impedance	50 Ohms
Inner Conductor Type	Stranded
Inner Conductor Material and Plating	Copper Clad Steel, Silver
Dielectric Type	PTFE
Number of Shields	1
Shield Layer 1	Silver Plated Copper Braid
Jacket Material	PTFE, White
Jacket Diameter	0.11 in [2.79 mm]

## SMA Female Bulkhead to SMB Plug Right Angle Cable Using RG188 Coax with HeatShrink, LF Solder



### PE3336LF/HS

#### Connectors

Description	Connector 1	Connector 2
Type	SMA Female Bulkhead	SMB Plug Right Angle
Specification	MIL-STD-348	MIL-STD-348A
Impedance	50 Ohms	50 Ohms
Configuration	Straight	Right Angle
Contact Material and Plating	Beryllium Copper, Gold	Beryllium Copper, Gold
Contact Plating Specification	MIL-G-45204	30 $\mu$ in minimum
Dielectric Type		PTFE
Outer Conductor Material and Plating	Brass, Nickel	Brass, Nickel
Outer Conductor Plating Specification		100 $\mu$ in minimum
Body Material and Plating	Brass, Nickel	Brass, Nickel
Body Plating Specification		100 $\mu$ in minimum

#### Environmental Specifications

**Compliance Certifications** (see [product page](#) for current document)

#### Plotted and Other Data

Notes:

## SMA Female Bulkhead to SMB Plug Right Angle Cable Using RG188 Coax with HeatShrink, LF Solder




### PE3336LF/HS

#### Typical Performance Data

#### How to Order

Part Number Configuration:

**PE3336LF/HS - xx uu**



Example: PE3336LF/HS-12 = 12 inches long cable  
PE3336LF/HS-100cm = 100 cm long cable

SMA Female Bulkhead to SMB Plug Right Angle Cable Using RG188 Coax with HeatShrink, LF Solder from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SMA Female Bulkhead to SMB Plug Right Angle Cable Using RG188 Coax with HeatShrink, LF Solder PE3336LF/HS](#)

URL: <https://www.pasternack.com/sma-female-bulkhead-to-smb-plug-cable-using-rg188-with-heatshrink-lf-solder-pe3336lf-hs-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

# PE3336LF/HS CAD Drawing

SMA Female Bulkhead to SMB Plug Right Angle Cable Using RG188 Coax with HeatShrink, LF Solder

