

SMA Male to SMA Male Cable 18 Inch Length Using RG174 Coax, RoHS

# **RF Cable Assemblies Technical Data Sheet**

### Configuration

- Connector 1: SMA Male
- Connector 2: SMA Male
- Cable Type: RG174

#### **Electrical Specifications**

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		1,000	MHz
VSWR			1.4:1	
Velocity of Propagation		66		%
Capacitance		30.8 [101.05]		pF/ft [pF/m]

#### **Specifications by Frequency**

Description	F1	F2	F3	F4	F5	Units
Frequency	50	100	250	500	1,000	MHz
Insertion Loss (Max.)	0.26	0.33	0.41	0.52	0.68	dB
VSWR (Max.)	1.4:1	1.4:1	1.4:1	1.4:1	1.4:1	
Return Loss (Max.)	15.56	15.563	15.563	15.563	15.563	dB

#### **Mechanical Specifications**

Cable Assembly Length Diameter	18 in [457.2 mm] 0.312 in [7.92 mm]
Weight	0.026 lbs [11.79 g]
Cable Cable Type	RG174
Impedance	50 Ohms
Inner Conductor Type	Stranded
Inner Conductor Material and Plating	Copper Clad Steel
Dielectric Type	PE (LD)
Number of Shields	1
Shield Layer 1	Tinned Copper Braid

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: SMA Male to SMA Male Cable 18 Inch Length Using RG174 Coax, RoHS PE3353LF-18

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 Phone: (866) 727-8376 or (949) 261-1920 • Fax: (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com



### PE3353LF-18



SMA Male to SMA Male Cable 18 Inch Length Using RG174 Coax, RoHS

### **RF Cable Assemblies Technical Data Sheet**

Jacket Material Jacket Diameter

#### Connectors

Description	Connector 1	Connector 2	
Туре	SMA Male	SMA Male	
Specification	MIL-STD-348A	MIL-STD-348A	
Impedance	50 Ohms	50 Ohms	
Contact Material and Plating	Brass, Gold	Brass, Gold	
Contact Plating Specification	30µ in. Minimum	30µ in. Minimum	
Dielectric Type	PTFE	PTFE	
Coupling Nut Material and Plating	Brass, Nickel	Brass, Nickel	
Coupling Nut Plating Specification	100µ in. Minimum	100µ in. Minimum	
Hex Size	5/16 in	5/16 in	
Torque	5 in-lbs [0.57 Nm]	5 in-lbs [0.57 Nm]	
Body Material and Plating	Brass, Nickel	Brass, Nickel	
Body Plating Specification	100µ in. Minimum	100µ in. Minimum	

#### **Environmental Specifications**

Temperature **Operating Range** 

-40 to +80 deg C

PVC, Black

0.1 in [2.54 mm]

Compliance Certifications (visit www.Pasternack.com for current document) **RoHS** Compliant Yes **REACH Compliant** 12/19/2011

#### **Plotted and Other Data**

Notes:

• Values at 25°C, sea level.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: SMA Male to SMA Male Cable 18 Inch Length Using RG174 Coax, RoHS PE3353LF-18

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 Phone: (866) 727-8376 or (949) 261-1920 • Fax: (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com



### PE3353LF-18




SMA Male to SMA Male Cable 18 Inch Length Using RG174 Coax, RoHS



## **RF Cable Assemblies Technical Data Sheet**

### PE3353LF-18



Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 Phone: (866) 727-8376 or (949) 261-1920 • Fax: (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com

PE3353LF-18 CAD Drawing SMA Male to SMA Male Cable 18 Inch Length Using RG174 Coax, RoHS

