



RF Cable Assemblies Technical Data Sheet

Sales@Pasternack.com • Techsupport@Pasternack.com

PE3353-36 REV 1.0

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 Phone: (866) 727-8376 or (949) 261-1920 • Fax: (949) 261-7451

Length Diameter

Mechanical Specifications Cable Assembly

Weight

Cable

Cable Type Impedance Inner Conductor Type Inner Conductor Material and Plating **Dielectric Type** Number of Shields Shield Layer 1

36 in [914.4 mm] 0.312 in [7.92 mm] 0.038 lbs [17.24 g]

RG174 50 Ohms Stranded **Copper Clad Steel** PE (LD) 1 **Tinned Copper Braid**

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: SMA Male to SMA Male Cable 36 Inch Length Using RG174 Coax PE3353-36

Specifications by Frequency

opecifications by requercy							
Description	F1	F2	F3	F4	F5	Units	
Frequency	50	100	250	500	1,000	MHz	
Insertion Loss (Max.)	0.33	0.45	0.61	0.84	1.16	dB	
VSWR (Max.)	1.4:1	1.4:1	1.4:1	1.4:1	1.4:1		
Return Loss (Max.)	15.56	15.563	15.563	15.563	15.563	dB	

Configuration

 Connector 1: SMA Male Connector 2: SMA Male Cable Type: RG174

ctrical Specifications				
Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		1,000	MHz
VSWR			1.4:1	
Velocity of Propagation		66		%
Capacitance		30.8 [101.05]		pF/ft [pF/m]







SMA Male to SMA Male Cable 36 Inch Length Using RG174 Coax

RF Cable Assemblies Technical Data Sheet

Jacket Material Jacket Diameter

PVC, Black 0.1 in [2.54 mm]

Connectors

Connector 1	Connector 2	
SMA Male	SMA Male	
MIL-STD-348A	MIL-STD-348A	
50 Ohms	50 Ohms	
Brass, Gold	Brass, Gold	
30µ in. Minimum	30µ in. Minimum	
PTFE	PTFE	
Brass, Nickel	Brass, Nickel	
100µ in. Minimum	100µ in. Minimum	
5/16 in	5/16 in	
5 in-lbs [0.57 Nm]	5 in-lbs [0.57 Nm]	
Brass, Nickel	Brass, Nickel	
100µ in. Minimum	100µ in. Minimum	
	SMA Male MIL-STD-348A 50 Ohms Brass, Gold 30µ in. Minimum PTFE Brass, Nickel 100µ in. Minimum 5/16 in 5 in-lbs [0.57 Nm] Brass, Nickel	

Environmental Specifications

Temperature

Operating Range

-40 to +80 deg C

Compliance Certifications (visit www.Pasternack.com for current document) For RoHS Compliant version, use PE3353LF-36. Contact Pasternack if product cannot be found. **REACH Compliant** 12/19/2011

Plotted and Other Data

Notes:

Values at 25°C, sea level.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: SMA Male to SMA Male Cable 36 Inch Length Using RG174 Coax PE3353-36

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 Phone: (866) 727-8376 or (949) 261-1920 • Fax: (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com



PE3353-36






SMA Male to SMA Male Cable 36 Inch Length Using RG174 Coax

RF Cable Assemblies Technical Data Sheet

PE3353-36



Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 Phone: (866) 727-8376 or (949) 261-1920 • Fax: (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com

PE3353-36 CAD Drawing SMA Male to SMA Male Cable 36 Inch Length Using RG174 Coax

