

## N Male to LC Male Cable Using RG393 Coax with HeatShrink

## RF Cable Assemblies Technical Data Sheet

PE33601/HS

**Configuration**

- Connector 1: N Male
- Connector 2: LC Male
- Cable Type: RG393
- Coax Flex Type: Flexible

**Features**

- 69.5% Phase Velocity
- Double Shielded
- FEP Jacket

**Applications**

- General Purpose
- Laboratory Use

**Description**

Pasternack's PE33601/HS type N male to LC male cable using RG393 coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack type N to LC cable assembly has a male to male gender configuration with 50 ohm flexible RG393 coax. The double shielding of this Pasternack cable assembly provides excellent shielding effectiveness.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

**Electrical Specifications**

Description	Minimum	Typical	Maximum	Units
Velocity of Propagation		69.5		%
Capacitance		29.4 [96.46]		pF/ft [pF/m]

**Mechanical Specifications****Cable Assembly**

Weight 0.566 lbs [256.73 g]

**Cable**

Cable Type RG393  
Impedance 50 Ohms  
Inner Conductor Type Stranded  
Inner Conductor Material and Plating Copper, Silver  
Dielectric Type PTFE  
Number of Shields 2

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [N Male to LC Male Cable Using RG393 Coax with HeatShrink PE33601/HS](#)

## N Male to LC Male Cable Using RG393 Coax with HeatShrink

## RF Cable Assemblies Technical Data Sheet

PE33601/HS

Shield Layer 1	Silver Plated Copper Braid
Shield Layer 2	Silver Plated Copper Braid
Jacket Material	FEP, Tan
Jacket Diameter	0.39 in [9.91 mm]
Repeated Minimum Bend Radius	3.9 in [99.06 mm]

## Connectors

Description	Connector 1	Connector 2
Type	N Male Threaded	LC Male Threaded
Specification	MIL-STD-348A	MIL-STD-348
Impedance	50 Ohms	50 Ohms
Contact Material and Plating	Brass, Gold	Silver
Contact Plating Specification	30 µin minimum	QQ-S-365
Dielectric Type	PTFE	PTFE
Body Material and Plating	Brass, Nickel	Brass, Nickel
Body Plating Specification	100 µin minimum	QQ-N-290
Coupling Nut Material and Plating	Brass, Nickel	Brass, Nickel
Coupling Nut Plating Specification	100 µin minimum	QQ-N-290

**Compliance Certifications** (see [product page](#) for current document)

## Plotted and Other Data

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [N Male to LC Male Cable Using RG393 Coax with HeatShrink PE33601/HS](#)

## N Male to LC Male Cable Using RG393 Coax with HeatShrink

**RF Cable Assemblies Technical Data Sheet****PE33601/HS****How to Order**

Part Number Configuration:

**PE33601/HS****- xx****uu**

Unit of Measure:  
cm = Centimeters  
<blank> = Inches  
Length  
Base Number

Example: PE33601/HS-12 = 12 inches long cable  
PE33601/HS-100cm = 100 cm long cable

N Male to LC Male Cable Using RG393 Coax with HeatShrink from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [N Male to LC Male Cable Using RG393 Coax with HeatShrink PE33601/HS](#)

URL: <https://www.pasternack.com/n-male-to-lc-male-cable-using-rg393-with-heatshrink-pe33601-hs-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PE33601/HS CAD Drawing  
N Male to LC Male Cable Using RG393 Coax with HeatShrink

